



SCALANCE XB213-3 managed Layer 2 IE Switch 13x 10/100 Mbps RJ45 ports, 3x MM FO ST port 1x console port, diagnostics LED, redundant power supply, IEC 62443-4-2 certified; temperature range 0 °C to +60 °C; DIN-rail mounting; PROFINET IO device; EtherNet/IP-compliant; default EtherNet/IP

product type designation	
product brand name	SCALANCE
product type designation	XB213-3
Technical Product Detail Page	https://i.siemens.com/1P6GK5213-3BB00-2TB2
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	13; RJ45
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	3
transmission method / of the optical interface	100BaseFX
interfaces / other	
number of electrical connections	
• for operator console	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for management purposes	RJ45
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	9.8 W
• supply voltage / 1 / voltage range	19.2 ... 28.8
• consumed current / 1 / maximum	0.41 A
• type of electrical connection / 1 / for power supply	6-pole terminal block
• product component / 1 / fusing at power supply input	Yes
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact

width	120 mm
height	117 mm
depth	109 mm
net weight	0.5 kg
material / of the enclosure	Polycarbonate (PC-GF10)
fastening method	
• 35 mm DIN-rail mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
network load class / according to PROFINET	III
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• SFTP	Yes
• BOOTP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	

product function	
• DHCP client	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes; LC mode
• of the PROFINET IO device / is supported / PROFINET system redundancy	No
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• passive listening	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• RADIUS client	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
• SSL	Yes
product functions / time	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4 (Class A)
• for immunity to EMC	EN 61000-6-2
• for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• RoHS conformity	Yes
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes

standards, specifications, approvals / Environmental Product Declaration		
Environmental Product Declaration	Yes	
global warming potential [CO2 eq]		
• total	347.88999 kg	
• during manufacturing	40.94 kg	
• during operation	306.44 kg	
• after end of life	0.51 kg	
product functions / general		
MTBF	45 a	
warranty period	5 a	
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022	
further information / internet links		
internet link		
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358	
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud	
• to website: Industrial communication	https://www.siemens.com/simatic-net	
• to web page: SiePortal	https://sieportal.siemens.com/	
• to website: Image database	https://www.automation.siemens.com/bilddb	
• to website: CAX-Download-Manager	https://www.siemens.com/cax	
• to website: Industry Online Support	https://support.industry.siemens.com	
security information		
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)	
Approvals / Certificates		
Environmental Product Declaration		
• global warming potential [CO2 eq] / during manufacturing	40.94 kg	
• global warming potential [CO2 eq] / during operation	306.44 kg	
• global warming potential [CO2 eq] / after end of life	0.51 kg	
• global warming potential [CO2 eq] / total	347.89 kg	
Environment	General Product Approval	
	 EG-Konf.	
		
	China RoHS	
	Declaration of Conformity	
	 CCC	
General Product Approval		
 UL	Declaration of Conformity	
	 RCM	
	TUEV	
	 EG-Konf.	
	China RoHS	
General Product Approval	EMV	For use in hazardous locations



[FM](#)

[CCC-Ex](#)

Radio Equipment
Type Approval Certificate

Industrial Communication



[PROFINET](#)

last modified:

5/9/2026