



SCALANCE XC224 manageable Layer 2 IE switch; IEC 62443-4-2 certified; 24x 10/100 Mbit/s RJ45 ports; 1x console port, diagnostics LED; redundant power supply; temperature range -40 °C to +70 °C; assembly: DIN rail/S7 mounting rail/wall Office redundancy functions features (RSTP, VLAN,...); PROFINET IO device Ethernet/IP-compliant, C-plug slot;

product type designation	
product brand name	SCALANCE
product type designation	XC224
Technical Product Detail Page	https://i.siemens.com/1P6GK5224-0BA00-2AC2
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	24; RJ45
number of 10/100 Mbit/s RJ45 ports	
• with securing collar	24
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	9 W
• consumed current / 1 / at rated supply voltage / maximum	0.375 A
• supply voltage / 1 / voltage range	9.6 ... 31.2
• consumed current / 1 / maximum	0.75 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	2,5 A / 125 V
ambient conditions	
ambient temperature	

- during operation - during storage - during transport	-40 ... +70 °C -40 ... +85 °C -40 ... +85 °C
relative humidity at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	120 mm
height	147 mm
depth	125 mm
net weight	0.88 kg
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method 35 mm DIN-rail mounting - wall mounting - S7-300 rail mounting - S7-1500 rail mounting	Yes Yes Yes Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.3~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function QoS according to DSCP	Yes
product feature - Cut Through switching method - Store & Forward switching method	No Yes
product functions / management, configuration, engineering	
product function - CLI - web-based management - MIB support - TRAPs via email - configuration with STEP 7 - RMON - SMTP server - port mirroring - multiport mirroring - CoS - PROFINET IO diagnosis - switch-managed	Yes Yes Yes Yes Yes Yes No Yes Yes Yes Yes Yes
PROFINET conformity class	B
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported - Telnet - HTTP - HTTPS - TFTP - SFTP - BOOTP - GMRP - DCP - LLDP - EtherNet/IP - SNMP v1 - SNMP v2 - SNMP v3 - IGMP (snooping/querier)	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes

identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	
product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes; LC mode
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• LACP	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• RADIUS client	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	

• SSH	Yes
• SSL	Yes
product functions / time	
product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• cULus approval	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
• for EMC interference emission	EN 61000-6-4, EN 50121-4
• for immunity to EMC	EN 61000-6-2, EN 50121-4
• for safety / from CSA and UL	UL 60950-1 E115352
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50121-4	Yes
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / marine classification	
certificate of suitability / shipbuilding approval / note	Certifications marked 'No' are currently under renewal.
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Chinese Classification Society (CCS)	No
• Det Norske Veritas (DNV)	Yes
• Korean Register of Shipping (KRS)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	No
• Royal Institution of Naval Architects (RINA)	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	441.1 kg
• during manufacturing	47.67 kg
• during operation	392.81999 kg
• after end of life	0.57 kg
product functions / general	
MTBF	41 a
warranty period	5 a

product function / is supported / identification link		Yes; acc. to IEC 61406-1:2022	
further information / internet links			
internet link			
- to website: Selection guide for cables and connectors - to web page: selection aid TIA Selection Tool - to website: Industrial communication - to web page: SiePortal - to website: Image database - to website: CAX-Download-Manager - to website: Industry Online Support		https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com	
security information			
security information		Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)	
Approvals / Certificates			
Environmental Product Declaration			
- global warming potential [CO2 eq] / during manufacturing - global warming potential [CO2 eq] / during operation - global warming potential [CO2 eq] / after end of life - global warming potential [CO2 eq] / total		47.67 kg 392.82 kg 0.57 kg 441.1 kg	
Environment		General Product Approval	
		 EG-Konf.	
		Declaration of Conformity	
		 CCC	
			
		China RoHS	
General Product Approval			
 UL		Declaration of Conformity	
		 RCM	
		TUEV	
		 EG-Konf.	
		China RoHS	
General Product Approval		EMV	
General Product Approval		For use in hazardous locations	
			
		 IECEX	
		 ATEX	
		FM	
		CCC-Ex	
Test Certificates			
Maritime application			
Type Test Certificates/Test Report			
 ABS			
 BUREAU VERITAS			
 DNV			
 LRS			
NK / Nippon Kaiji Kyokai			



[PROFINET](#)

last modified:

5/9/2026 