



circuit breaker 3VA5 UL Frame 125 breaking capacity class M 35 kA @ 480 V 4-pole, line protection TM230, FTAM,  $I_n=125$  A overload protection  $I_r=125$  A permanently set short-circuit protection  $I_i=5...10 \times I_n$  neutral conductor protection 100% without connection

| Model                                                                                                                      |                             |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| product brand name                                                                                                         | SETRON                      |
| product designation                                                                                                        | Molded-case circuit breaker |
| product designation / according to UL file                                                                                 | MEAS                        |
| design of the product                                                                                                      | System protection           |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes                         |
| design of the load switch / according to UL 489 / High-Intensity-Discharge circuit breaker (HID Type)                      | No                          |
| design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type)                                | No                          |
| design of the overcurrent release                                                                                          | TM230                       |
| protection function of the overcurrent release                                                                             | LI                          |
| number of poles                                                                                                            | 4                           |
| General technical data                                                                                                     |                             |
| insulation voltage / rated value                                                                                           | 800 V                       |
| operating voltage / at DC / rated value                                                                                    | 600 V                       |
| operating voltage / at AC / rated value                                                                                    | 690 V                       |
| power loss [W] / maximum                                                                                                   | 29 W                        |
| power loss [W] / for rated value of the current / at AC / in hot operating state / per pole                                | 9.7 W                       |
| mechanical service life (operating cycles) / typical                                                                       | 20 000                      |
| electrical endurance (operating cycles) / at AC-1 / at 380/415 V                                                           | 8 000                       |
| electrical endurance (operating cycles) / at AC-1 / at 690 V                                                               | 4 000                       |
| electrical endurance (operating cycles) / at 480 V                                                                         | 8 000                       |
| electrical endurance (operating cycles) / at 600 V                                                                         | 4 000                       |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof                      | No                          |
| product function                                                                                                           |                             |
| • communication function                                                                                                   | No                          |
| • other measurement function                                                                                               | No                          |
| Net Weight                                                                                                                 | 1.05 g                      |
| Current                                                                                                                    |                             |
| marking / according to UL 489 / 100%-rated breaker                                                                         | No                          |
| operational current                                                                                                        |                             |
| • at 40 °C                                                                                                                 | 125 A                       |
| • at 45 °C                                                                                                                 | 122 A                       |
| • at 50 °C                                                                                                                 | 119 A                       |
| • at 55 °C                                                                                                                 | 117 A                       |
| • at 60 °C                                                                                                                 | 114 A                       |

|                                                                                                                                                                                                  |                                                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at 65 °C</li> <li>• at 70 °C</li> </ul>                                                                                                                 | 112 A<br>109 A                                                                                                                                                 |
| <b>Switching capacity according to IEC 60947</b>                                                                                                                                                 |                                                                                                                                                                |
| switching capacity class of the circuit breaker                                                                                                                                                  | M                                                                                                                                                              |
| maximum short-circuit current breaking capacity (I <sub>cu</sub> ) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>                          | 85 kA<br>55 kA<br>7 kA                                                                                                                                         |
| operating short-circuit current breaking capacity (I <sub>cs</sub> ) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>                        | 85 kA<br>55 kA<br>5 kA                                                                                                                                         |
| short-circuit current making capacity (I <sub>cm</sub> ) <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>                                    | 187 kA<br>121 kA<br>11.9 kA                                                                                                                                    |
| design of short-circuit protection                                                                                                                                                               | For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter |
| <b>Switching capacity according to UL 489</b>                                                                                                                                                    |                                                                                                                                                                |
| current breaking capacity <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 480 V</li> <li>• at 600 Y/347 V</li> </ul>                                                             | 85 kA<br>35 kA<br>18 kA                                                                                                                                        |
| <b>Adjustable parameters</b>                                                                                                                                                                     |                                                                                                                                                                |
| adjustable response value setting current (I <sub>r</sub> ) / of the L-trip / with I <sub>2t</sub> characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul> | 125 A<br>125 A                                                                                                                                                 |
| adjustable response value delay time (t <sub>r</sub> ) / for L-tripping / with I <sub>2t</sub> characteristic <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>     | 1 s<br>1 s                                                                                                                                                     |
| adjustable response value setting current (I <sub>i</sub> ) / for I-tripping <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                      | 625 A<br>1 250 A                                                                                                                                               |
| adjustable setting current (I <sub>nN</sub> ) / for N-tripping <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                    | 125 A<br>125 A                                                                                                                                                 |
| design of the N-conductor protection                                                                                                                                                             | 100%                                                                                                                                                           |
| product function / grounding protection                                                                                                                                                          | No                                                                                                                                                             |
| <b>Mechanical Design</b>                                                                                                                                                                         |                                                                                                                                                                |
| product component <ul style="list-style-type: none"> <li>• undervoltage release</li> <li>• voltage trigger</li> <li>• trip indicator</li> </ul>                                                  | No<br>No<br>No                                                                                                                                                 |
| height [in]                                                                                                                                                                                      | 5.51 in                                                                                                                                                        |
| height                                                                                                                                                                                           | 140 mm                                                                                                                                                         |
| width [in]                                                                                                                                                                                       | 4 in                                                                                                                                                           |
| width                                                                                                                                                                                            | 101.5 mm                                                                                                                                                       |
| depth [in]                                                                                                                                                                                       | 3.01 in                                                                                                                                                        |
| depth                                                                                                                                                                                            | 76.5 mm                                                                                                                                                        |
| <b>Connections</b>                                                                                                                                                                               |                                                                                                                                                                |
| arrangement of electrical connectors / for main current circuit                                                                                                                                  | Without connection                                                                                                                                             |
| type of electrical connection / for main current circuit                                                                                                                                         | Without                                                                                                                                                        |
| <b>Auxiliary circuit</b>                                                                                                                                                                         |                                                                                                                                                                |
| number of CO contacts / for auxiliary contacts                                                                                                                                                   | 0                                                                                                                                                              |
| <b>Accessories</b>                                                                                                                                                                               |                                                                                                                                                                |
| product extension / optional / motor drive                                                                                                                                                       | Yes                                                                                                                                                            |
| <b>Environmental conditions</b>                                                                                                                                                                  |                                                                                                                                                                |

|                                           |        |
|-------------------------------------------|--------|
| protection class IP / on the front        | IP40   |
| ambient temperature                       |        |
| • during operation / minimum              | -25 °C |
| • during operation / maximum              | 70 °C  |
| • during storage / minimum                | -40 °C |
| • during storage / maximum                | 80 °C  |
| reference code / according to IEC 81346-2 | Q      |

#### Approvals / Certificates

##### General Product Approval



[Miscellaneous](#)



[Miscellaneous](#)



##### General Product Approval

EMV



[Confirmation](#)



##### Test Certificates

##### Maritime application

##### other

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



[Miscellaneous](#)

[Confirmation](#)

##### Environment

[Environmental Conformations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA5112-5GC41-0AA0>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA5112-5GC41-0AA0>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA5112-5GC41-0AA0](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA5112-5GC41-0AA0)

##### CAX-Online-Generator


<https://www.siemens.com/cax>

##### Tender specifications

<https://www.siemens.com/specifications>

##### Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>)





last modified:

4/23/2026

