

SCALANCE XR524-8C; managed IE switch; layer 3 with Key-Plug available; power supply 2x 230 V AC; 24x 10/100/1000 Mbit/s RJ45; 8x 100/1000 Mbit/s SFP; contains 8 combo ports; in total 24 ports can be used; error signaling contact; select/set pushbutton; PROFINET IO device; redundancy functions; Office features (RSTP, VLAN, IGMP, ...); C-PLUG in scope of supply.



product type designation	
product brand name	SCALANCE
product type designation	XR524-8C
Technical Product Detail Page	https://i.siemens.com/1P6GK5524-8GS00-4AR2
transfer rate	
transfer rate	10, 100, 1000 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	24; RJ45
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	0
number of electrical connections	
• for SFP	8
number of combo ports / with RJ45 interface for optical plug-in transceiver	8
interfaces / for communication / plug-in	
number of electrical connections	
• for SFP	8
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for management purposes	RJ45
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
product feature / hot-swappable interface modules	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	Yes
type of voltage / 1 / of the supply voltage	AC
• supply voltage / 1 / rated value	230 V
• power loss [W] / 1 / rated value	24 W

<ul style="list-style-type: none"> • supply voltage / 1 / voltage range • consumed current / 1 / maximum • type of electrical connection / 1 / for power supply • product component / 1 / fusing at power supply input • fuse protection type / 1 / at input for supply voltage 	<p>90 ... 264</p> <p>0.6 A</p> <p>4-pole terminal block</p> <p>Yes</p> <p>3,15 A / 250 V</p>
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport 	<p>-25 ... +60 °C</p> <p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p>
relative humidity	
<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	19-inch rack
number of modular height units / relating to 19-inch cabinet	1
width	449 mm
height	44 mm
depth	305 mm
net weight	4.5 kg
fastening method	
<ul style="list-style-type: none"> • 19-inch installation • 35 mm DIN-rail mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting 	<p>Yes</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p>
type of cable outlet	Cable outlet at front
product features, product functions, product components / general	
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
<ul style="list-style-type: none"> • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • RMON • port mirroring • multiport mirroring • CoS • PROFINET IO diagnosis • switch-managed 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
PROFINET conformity class	B
telegram length / for Ethernet / maximum	9216 byte
protocol / is supported	
<ul style="list-style-type: none"> • Telnet • HTTP • HTTPS • TFTP • FTP • BOOTP • GMRP • DCP • LLDP • SNMP v1 • SNMP v2 • SNMP v3 • IGMP (snooping/querier) 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>

identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	Yes
• VLAN - IP-based	Yes
• VLAN dynamic	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / routing	
service / routing / note	IP routing in combination with KEY-PLUG XR-500
product function	
• static IP routing	Yes
• static IP routing IPv6	Yes
• dynamic IP routing	Yes
• dynamic IP routing IPv6	Yes
protocol / is supported	
• RIPv2	Yes
• RIPnG for IPv6	Yes
• OSPFv2	Yes
• OSPFv3 for IPv6	Yes
• VRRP	Yes
• VRRP for IPv6	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes; LC mode
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• redundancy procedure MSTP	Yes
• passive listening	Yes
protocol / is supported	
• LACP	Yes
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes

<ul style="list-style-type: none"> • broadcast/multicast/unicast limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • UKCA marking 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • Regulatory Compliance Mark (RCM) 	Yes
standard	
<ul style="list-style-type: none"> • for EMC interference emission 	EN 61000-6-4 (Class A)
<ul style="list-style-type: none"> • for immunity to EMC 	EN 61000-6-2
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1; CSA C22.2 No. 213-M1987
standards, specifications, approvals / other	
certificate of suitability	
<ul style="list-style-type: none"> • RoHS conformity 	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
<ul style="list-style-type: none"> • total 	436.68 kg
<ul style="list-style-type: none"> • during manufacturing 	207 kg
<ul style="list-style-type: none"> • during operation 	228.75 kg
<ul style="list-style-type: none"> • after end of life 	0.93 kg
product functions / general	
warranty period	5 a
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors 	https://support.industry.siemens.com/cs/ww/en/view/109766358
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	https://www.siemens.com/tstcloud
<ul style="list-style-type: none"> • to website: Industrial communication 	https://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to web page: SiePortal 	https://sieportal.siemens.com/
<ul style="list-style-type: none"> • to website: Image database 	https://www.automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAX-Download-Manager 	https://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates,

subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

Environmental Product Declaration

• global warming potential [CO2 eq] / during manufacturing	207 kg
• global warming potential [CO2 eq] / during operation	228.75 kg
• global warming potential [CO2 eq] / after end of life	0.93 kg
• global warming potential [CO2 eq] / total	436.68 kg

Environment

General Product Approval



EG-Konf.

[Declaration of Conformity](#)



CCC



General Product Approval

EMV

Maritime application

[China RoHS](#)

[Special Test Certificate](#)



RCM

[China RoHS](#)



ABS

Maritime application



LRS

[NK / Nippon Kaiji Kyokai](#)



PRS



RINA

Industrial Communication

[PROFINET](#)

last modified:

5/9/2026