

product type designation	W734-1 RJ45 (USA)
	IWLAN client, SCALANCE W734-1, RJ45, 1 radio, 2 R-SMA antenna port, iFeatures support via KEY-PLUG, IEEE 802.11a/b/g/h/n, 2.4/5 GHz, gross data rate 300 Mbps, 2x RJ45 max. 100 Mbps, PoE integrated 2-port switch, redundant 24 V DC, joint block, IP30, -20... 60 °C, plug slot WPA2/802.11i/e, observe national approvals! CERT ID: MSN-W1-RJ-E2, FCC ID: LYHMSN1V1, scope of supply: manuals on CD-ROM, German/English, 1x joint block; only for operation in the USA
product brand name	SCALANCE
Technical Product Detail Page	https://i.siemens.com/1P6GK5734-1FX00-0AB0
transfer rate	
transfer rate	
• with WLAN / maximum	300 Mbit/s
• for Industrial Ethernet	10, 100 Mbit/s
interfaces	
number of electrical connections	
• for network components or terminal equipment	2
• for power supply	1
• for redundant voltage supply	1
type of electrical connection	
• for network components or terminal equipment	RJ45 socket
• for power supply	4-pole screw terminal, PoE
memory	
design of the removable storage	
• C-PLUG	Yes
• KEY-PLUG	Yes
interfaces / wireless	
number of radio cards / permanently installed	1
transmission mode / for multiple input multiple output (MIMO)	2x2
number of spatial streams	2
number of electrical connections / for external antenna(s)	2
type of electrical connection / for external antenna(s)	R-SMA (socket)
product feature / external antenna can be mounted directly on device	Yes
supply voltage, current consumption, power loss	
type of voltage / of the supply voltage	DC
supply voltage	
• from Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af	48 V
consumed current	
• at DC / at 24 V / typical	0.25 A
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	0.125 A
power loss [W]	
• at DC / at 24 V / typical	6 W
• with Power-over-Ethernet according to IEEE802.3at for type 1 and IEEE802.3af / typical	6 W
supply voltage / 1	
• from terminal block	19.2 V
supply voltage / 2	
• from terminal block	28.8 V
ambient conditions	
ambient temperature	
• during operation	-20 ... +60 °C

during storage	-40 ... +85 °C
during transport	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W774-1 RJ45 or W734-1 RJ45 product must be installed in an enclosure. To comply with EN 50021, this enclosure must meet the requirements of at least IP 54 in compliance with EN 60529.
protection class IP	IP30
design, dimensions and weights	
width	26 mm
height	156 mm
depth	127 mm
width / of the enclosure / without antenna	26 mm
height / of the enclosure / without antenna	147 mm
depth / of the enclosure / without antenna	127 mm
net weight	0.52 kg
fastening method	wall mounting only if flat mounted
S7-300 rail mounting	Yes
S7-1500 rail mounting	Yes
35 mm DIN-rail mounting	Yes
wall mounting	Yes
radio frequencies	
operating frequency	
for WLAN in 2.4 GHz frequency band	2.41 ... 2.48 GHz; depending on the country approvals
for WLAN in 5 GHz frequency band	4.9 ... 5.8 GHz; depending on the country approvals
product features, product functions, product components / general	
product function / Access Point Mode	No
product function / client Mode	Yes
product function	
iPCF client	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
iPCF-MC client	Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iPCF-capable radio modules	1
product function / iPRP	Yes; In combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures' only
product functions / management, configuration, engineering	
number of manageable IP addresses / in client	8
product function	
CLI	Yes
web-based management	Yes
MIB support	Yes
TRAPs via email	Yes
configuration with STEP 7	Yes
configuration with STEP 7 in the TIA Portal	Yes
WDS	No
protocol / is supported	
Address Resolution Protocol (ARP)	Yes
ICMP	Yes
Telnet	Yes
HTTP	Yes
HTTPS	Yes
TFTP	Yes
DCP	Yes
LLDP	No
identification & maintenance function	
I&M0 - device-specific information	Yes
I&M1 - higher level designation/location designation	Yes
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
product functions / diagnostics	

product function	
• PROFINET IO diagnosis	Yes
• link check	No
• connection monitoring IP-Alive	No
• SysLog	Yes
protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
product functions / VLAN	
product function	
• function VLAN with IWLAN	No
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP server	Yes
• DHCP Option 82	Yes
product functions / redundancy	
protocol / is supported	
• STP/RSTP	Yes
• MSTP	Yes
• RSTP	Yes
product functions / security	
product function	
• ACL - MAC-based	Yes
• management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	Yes
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
protocol / is supported	
• SSH	Yes
• RADIUS	Yes
product functions / time	
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• SIMATIC time synchronization (SIMATIC Time)	Yes
standards, specifications, approvals	
standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4, FM16US0205X
• for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
certificate of suitability	
• EC Declaration of Conformity	Yes
• CE marking	Yes
• C-Tick	Yes
• E1 approval	No
• railway application in accordance with EN 50155	No
• NEMA TS2	No
• IEC 61375	No
• IEC 61850-3	No
• NEMA4X	No
• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	Yes
• Power-over-Ethernet according to IEEE802.3at for type 2	Yes
standard for wireless communication	
• IEEE 802.11a	Yes

• IEEE 802.11b • IEEE 802.11e • IEEE 802.11g • IEEE 802.11h • IEEE 802.11i • IEEE 802.11n	Yes Yes Yes Yes Yes Yes
wireless approval	You will find the current list of countries at: www.siemens.de/funkzulassungen
standards, specifications, approvals / marine classification	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Korean Register of Shipping (KRS) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) • Royal Institution of Naval Architects (RINA)	Yes Yes Yes Yes Yes Yes Yes Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• from CSA and UL	ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, Cl. 1, div. 2, GP. A, B, C, D, T4 / Cl. 1, Zone 2, GP IIC E240480
certificate of suitability / CCC / for hazardous zone according to GB standard	Yes; GB3836.1, GB3836.8
• as marking	Ex nA IIC T4 Gc
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total • during manufacturing • during operation • after end of life	195.91999 kg 29.7 kg 166.06 kg 0.16 kg
accessories	
accessories	24 V DC screw terminal included in scope of delivery
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to web page: WLAN country approval • to the website: IWLAN • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/wireless-approvals https://www.siemens.com/iwlan https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under

Approvals / Certificates

General Product Approval



[Declaration of Con-
formity](#)



[Manufacturer Declara-
tion](#)

[China RoHS](#)

General Product Ap-
proval

For use in hazardous locations

Radio Equipment
Type Approval Certi-
ficate

[China RoHS](#)



[FM](#)

[CCC-Ex](#)

[Miscellaneous](#)

Maritime application



[NK / Nippon Kaiji Ky-
okai](#)



Maritime application

Environment



last modified:

5/9/2026 