

product type designation



W778-1 M12 EEC

IWLAN access point, SCALANCE W778-1 M12 EEC, 1 radio, 2 N-CON antenna port, iFeatures support via KEY-PLUG, IEEE 802.11a/b/g/h/n, 2.4/5 GHz, gross data rate 300 Mbps, 2x M12 max. 100 Mbps, PoE integrated 2-port switch, redundant 24 V DC, M12 A-coded IP65, -30...+75 °C, plug slot WPA2/802.11i/e, conformal coating EN 50155, EN45545, observe national approvals! CERT ID: MSN65-W1-M12-E2 scope of supply: manuals on CD-ROM, German/English, M12 sealing caps, for operation outside of USA/Israel

product brand name

SCALANCE

Technical Product Detail Page

<https://l.siemens.com/1P6GK5778-1GY00-0TA0>

transfer rate

transfer rate

- | | |
|---------------------------|----------------|
| • with WLAN / maximum | 300 Mbit/s |
| • for Industrial Ethernet | 10, 100 Mbit/s |

interfaces

number of electrical connections

- | | |
|--|---|
| • for network components or terminal equipment | 2 |
| • for power supply | 1 |
| • for redundant voltage supply | 1 |

type of electrical connection

- | | |
|--|--------------------------------------|
| • for network components or terminal equipment | M12 interface (4-pole, D-coded), PoE |
| • for power supply | M12 interface (4-pole, A-coded) |

memory

design of the removable storage

- | | |
|------------|-----|
| • C-PLUG | Yes |
| • KEY-PLUG | Yes |

interfaces / wireless

number of radio cards / permanently installed

1

transmission mode / for multiple input multiple output (MIMO)

2x2

number of spatial streams

2

number of electrical connections / for external antenna(s)

2

type of electrical connection / for external antenna(s)

N-Connect (socket)

product feature / external antenna can be mounted directly on device

Yes

supply voltage, current consumption, power loss

type of voltage / of the supply voltage

DC

supply voltage

- | | |
|--|------|
| • from Power-over-Ethernet according to IEEE802.3af for type 1 and IEEE802.3af | 48 V |
|--|------|

consumed current

- | | |
|--|---------|
| • at DC / at 24 V / typical | 0.25 A |
| • with Power-over-Ethernet according to IEEE802.3af for type 1 and IEEE802.3af / typical | 0.125 A |

power loss [W]

- | | |
|--|-----|
| • at DC / at 24 V / typical | 6 W |
| • with Power-over-Ethernet according to IEEE802.3af for type 1 and IEEE802.3af / typical | 6 W |

supply voltage / 1 • from M12 Power Connector (A-coded) for redundant power supply	16.8 V
supply voltage / 2 • from M12 Power Connector (A-coded) for redundant power supply	31.2 V
ambient conditions	
ambient temperature • during operation • during storage • during transport	-40 ... +75 °C -40 ... +85 °C -40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
ambient condition / for operation	When used under hazardous conditions (Zone 2), the SCALANCE W778-1 M12 or W738-1 M12 product must be installed in an housing with at least IP54 degree of protection according to EN 60529 within the scope of EN 50021.
protection class IP	IP65
design, dimensions and weights	
width	140 mm
height	160 mm
depth	45 mm
width / of the enclosure / without antenna	140 mm
height / of the enclosure / without antenna	149 mm
depth / of the enclosure / without antenna	45 mm
net weight	0.95 kg
product feature / conformal coating	Yes
fastening method • S7-300 rail mounting • S7-1500 rail mounting • 35 mm DIN-rail mounting • wall mounting	35 mm DIN rail mounting only per accessories No No Yes Yes
radio frequencies	
operating frequency • for WLAN in 2.4 GHz frequency band • for WLAN in 5 GHz frequency band	2.41 ... 2.48 GHz; depending on the country approvals 4.9 ... 5.8 GHz; depending on the country approvals
product features, product functions, product components / general	
product function / Access Point Mode	Yes
product function / client Mode	Yes
number of SSIDs	4
product function • iPCF Access Point • iPCF client • iPCF-MC Access Point • iPCF-MC client	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures' No Yes; Only in combination with 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iPCF-capable radio modules	1
product function / iREF	Yes; Only in combination with the 'KEY-PLUG W780 iFeatures' or 'KEY-PLUG W740 iFeatures'
number of iREF-capable radio modules	1
product function / iPRP	Yes; In combination with the 'KEY-PLUG W780 iFeatures' only
product functions / management, configuration, engineering	
number of manageable IP addresses / in client	8
product function • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • configuration with STEP 7 in the TIA Portal • operation with IWLAN controller	Yes Yes Yes Yes Yes Yes No

• operation with Enterasys WLAN controller	No
• forced roaming on IP down with IWLAN	Yes
• forced roaming on link down with IWLAN	Yes
• WDS	Yes
protocol / is supported	
• Address Resolution Protocol (ARP)	Yes
• ICMP	Yes
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• DCP	Yes
• LLDP	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
product functions / diagnostics	
product function	
• PROFINET IO diagnosis	Yes
• link check	No
• connection monitoring IP-Alive	No
• localization via Aeroscout	Yes
• SysLog	Yes
protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
product functions / VLAN	
product function	
• function VLAN with IWLAN	Yes
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP server	Yes
• DHCP Option 82	Yes
product functions / redundancy	
protocol / is supported	
• STP/RSTP	Yes
• MSTP	Yes
• RSTP	Yes
product functions / security	
product function	
• ACL - MAC-based	Yes
• management security, ACL-IP based	Yes
• IEEE 802.1x (radius)	Yes
• NAT/NAPT	Yes
• access protection according to IEEE802.11i	Yes
• WPA/WPA2	Yes
• TKIP/AES	Yes
protocol / is supported	
• SSH	Yes
• RADIUS	Yes
product functions / time	
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• SIMATIC time synchronization (SIMATIC Time)	Yes

standards, specifications, approvals

standard	
• for FM	FM 3611: Class I, Division 2, Groups A,B,C,D, T4 / Class 1, Zone 2, Group IIC, T4, FM16US0205X
• for safety / from CSA and UL	UL 61010-2-201 E85972, CSA C22.2 no. 60950-1
certificate of suitability	
• EC Declaration of Conformity	Yes
• CE marking	Yes
• C-Tick	Yes
• E1 approval	Yes
• railway application in accordance with EN 50155	Yes
• railway application in accordance with EN 50121-4	Yes
• fire protection in accordance with EN 45545-2	Yes
• NEMA TS2	No
• IEC 61375	No
• IEC 61850-3	No
• NEMA4X	No
• Power-over-Ethernet according IEEE802.3at for type 1 and IEEE802.3af	Yes
• Power-over-Ethernet according to IEEE802.3at for type 2	Yes
standard for wireless communication	
• IEEE 802.11a	Yes
• IEEE 802.11b	Yes
• IEEE 802.11e	Yes
• IEEE 802.11g	Yes
• IEEE 802.11h	Yes
• IEEE 802.11i	Yes
• IEEE 802.11n	Yes
wireless approval	You will find the current list of countries at: www.siemens.de/funkzulassungen

standards, specifications, approvals / marine classification

Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	Yes
• DNV GL	Yes
• Korean Register of Shipping (KRS)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	Yes
• Royal Institution of Naval Architects (RINA)	Yes

standards, specifications, approvals / hazardous environments

standard / for hazardous zone	EN 60079-15:2005, EN 60079-0:2006, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• from CSA and UL	ANSI/ISA 12.12.01-2013, CAN/CSA C22.2 No.213-M1987, Cl. 1, div. 2, GP. A, B, C, D, T4 / Cl. 1, Zone 2, GP IIC E240480
certificate of suitability / CCC / for hazardous zone according to GB standard	Yes; GB3836.1, GB3836.8
• as marking	Ex nA IIC T4 Gc

standards, specifications, approvals / Environmental Product Declaration

Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	199.94999 kg
• during manufacturing	33.7 kg
• during operation	166.06 kg
• after end of life	0.19 kg

further information / internet links

internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to web page: WLAN country approval	https://www.siemens.com/wireless-approvals
• to the website: IWLAN	https://www.siemens.com/iwlan

- to website: Industrial communication
- to web page: SiePortal
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<https://www.siemens.com/simatic-net>
<https://sieportal.siemens.com/>
<https://www.automation.siemens.com/bilddb>
<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



[Declaration of Conformity](#)



[Manufacturer Declaration](#)

[Type Examination Certificate](#)

General Product Approval

For use in hazardous locations

[TUEV](#)

[China RoHS](#)



For use in hazardous locations

Radio Equipment Type Approval Certificate

[CCC-Ex](#)

[Miscellaneous](#)

SUBTEL



[Miscellaneous](#)

[Miscellaneous](#)

Maritime application



[NK / Nippon Kaiji Kyokai](#)



Railway

Environment

[Confirmation](#)



last modified:

5/9/2026

