



Buzzer element, continuous tone or pulsating, adjustable, 85 dB, black, 24 V AC/DC, diameter 70 mm

product brand name	SIRIUS
product designation	Buzzer element
General technical data	
product function adjustable acoustic signal	Yes
type of voltage of the operating voltage	AC/DC
operating voltage	
• 1 at DC rated value	24 V
• 1 at AC at 50 Hz rated value	24 V
• 1 at AC at 60 Hz rated value	24 V
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage	-10 %
consumed current maximum	25 mA
tone frequency	
• 1	1.75 kHz
reference code according to EN 61346-2	P
Acoustic signal	
type of acoustic signal	continuous tone / pulse tone
service life of acoustic signal device	5 000 h
loudness level	85 dB
loudness level	85 dB
tone frequency of alternating tone	1.75 kHz
Enclosure	
height	72 mm
width	70 mm
outer diameter of the signal column element	70 mm
material	PC
color	black
fastening method	Bayonet
protection class IP	IP65
Ambient conditions	
ambient temperature during operation	-20 ... +50 °C
Approvals Certificates	
General Product Approval	other



[Confirmation](#)



[Confirmation](#)

[Confirmation](#)[Environmental Confirmations](#)Siemens
EcoTech

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD4420-0FA>



Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD4420-0FA>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD4420-0FA>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD4420-0FA&lang=en

-P



last modified:

4/1/2025 