

circular conduc. terminal TA5.1 2 x 150...300 mm² for 2 cables; 3 units accessory for: plug-in unit 3VA9603-0KP00 3VA15/25/26

Model	
product brand name	SENTRON
product designation	circular conductor terminal 3 units
design of the product	Connection method
accessories	Wire connector
General technical data	
designation / of the terminal	TA5.1
type of electrical connection / with control wire tap	No
Mechanical Design	
Net Weight	1.039 kg
Connections according IEC	
connectable conductor cross-section	
• for copper cable / stranded / minimum	150 mm ²
• for copper cable / stranded / maximum	300 mm ²
• for aluminum cable / stranded / minimum	150 mm ²
• for aluminum cable / stranded / maximum	300 mm ²
stripped length	45 mm
tightening torque / when using copper cables	
• stranded	150 - 300 mm ² : 30 Nm
• finely stranded	150 - 240 mm ² : 30 Nm
• finely stranded / with core end processing	150 - 185 mm ² : 30 Nm
Connections according UL	
stripped length	1.77 in
Certificates	
General Product Approval	EMV

[Miscellaneous](#)



[Confirmation](#)



Test Certificates	Maritime application	other	Environment		
Type Test Certificates/Test Report		Miscellaneous	Confirmation	Environmental Confirmations	Environmental Confirmations

Environment



Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9603-0JJ25>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9603-0JJ25>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9603-0JJ25

CAX-Online-Generator

<https://www.siemens.com/cax>

Tender specifications

<https://www.siemens.com/specifications>

last modified:

4/6/2026 