



discharge reactor; Un(V): 690; Irms(A): 0.02

Figure similar

General technical data	
product designation	Quick discharge reactor
phase number	3
type of voltage	AC
operating voltage rated value	
• maximum	690 V
operating frequency rated value	
• maximum	0 Hz
current	
• at AC maximum	0.02 A
Mechanical data	
type of electrical connection for main current circuit	screw-type terminals
width	0.045 m
height	0.09 m
depth	0.06 m
Ambient conditions	
thermal class according to IEC 60085	B
ambient temperature rated value	40 °C
protection class IP	IP00
Approvals Certificates	
other	

[Confirmation](#)



Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4EJ9900-0EG
Cax online generator https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EJ9900-0EG
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/4EJ9900-0EG
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

last modified:

4/8/2025 