



Figure similar

line reactor for frequency converter; phases: 3; Un1(V): 500; Ithmax 1(A) / F1(Hz): 5 / 50; I LN (A): 4.5; UK(%): 2; LN(MH): 3.68; temperature rise/insulation class: 40 /B; IP00; connection: screw/flat-type connection; EN 61558-2-20 >UL/CSA-recognized< >reactor<

General technical data		
product designation		Netzdrossel f. FU
phase number		3
type of voltage		AC
operating voltage rated value	V	500
operating frequency rated value	Hz	50
•		
— operational current at AC rated value	A	4.5
— current at AC maximum	A	5
inductivity rated value	H	0.0037
relative inductive drop in voltage for rated value of the current, voltage and frequency	%	2
power loss [W] of the coil	W	11.5
power loss [W] of the iron core	W	5.6
Mechanical data		
type of electrical connection for main current circuit		screw-type terminals / tab terminals
width	m	0.088
height	m	0.108
depth	m	0.057
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00
Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)



[Environmental Confirmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
 Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
 Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
 Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4EP3200-2US00>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EP3200-2US00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EP3200-2US00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EP3200-2US00&lang=en

last modified:

4/8/2025 