

Reversing motor starter, Size 0, Three phase full voltage, Solid-state overload relay, OLR amp range 0.75-3.4A, 110V 50Hz / 120V 60Hz coil, Non-combination type, Enclosure type 4X fiberglass, Water/dust tight noncorrosive, Standard width enclosure

|                                                                          |                                      |
|--------------------------------------------------------------------------|--------------------------------------|
| product brand name                                                       | Class 22                             |
| design of the product                                                    | Full-voltage reversing motor starter |
| special product feature                                                  | ESP200 overload relay                |
| <b>General technical data</b>                                            |                                      |
| weight [lb]                                                              | 17 lb                                |
| Height x Width x Depth [in]                                              | 24 × 15 × 7 in                       |
| touch protection against electrical shock                                | NA for enclosed products             |
| installation altitude [ft] at height above sea level maximum             | 6560 ft                              |
| ambient temperature [°F]                                                 |                                      |
| • during storage                                                         | -22 ... +149 °F                      |
| • during operation                                                       | -4 ... +104 °F                       |
| ambient temperature                                                      |                                      |
| • during storage                                                         | -30 ... +65 °C                       |
| • during operation                                                       | -20 ... +40 °C                       |
| country of origin                                                        | USA                                  |
| <b>Horsepower ratings</b>                                                |                                      |
| yielded mechanical performance [hp] for 3-phase AC motor                 |                                      |
| • at 200/208 V rated value                                               | 0.5 hp                               |
| • at 220/230 V rated value                                               | 0.75 hp                              |
| • at 460/480 V rated value                                               | 1.5 hp                               |
| • at 575/600 V rated value                                               | 2 hp                                 |
| <b>Contactors</b>                                                        |                                      |
| size of contactor                                                        | NEMA controller size 0               |
| number of NO contacts for main contacts                                  | 3                                    |
| operating voltage for main current circuit at AC at 60 Hz maximum        | 600 V                                |
| operational current at AC at 600 V rated value                           | 18 A                                 |
| mechanical service life (operating cycles) of the main contacts typical  | 10000000                             |
| <b>Auxiliary contact</b>                                                 |                                      |
| number of NC contacts at contactor for auxiliary contacts                | 0                                    |
| number of NO contacts at contactor for auxiliary contacts                | 1                                    |
| number of total auxiliary contacts maximum                               | 8                                    |
| contact rating of auxiliary contacts of contactor according to UL        | 345VA@115VAC / 768VA@240VAC          |
| <b>Coil</b>                                                              |                                      |
| type of voltage of the control supply voltage                            | AC                                   |
| control supply voltage                                                   |                                      |
| • at AC at 50 Hz rated value                                             | 110 V                                |
| • at AC at 60 Hz rated value                                             | 120 V                                |
| holding power at AC minimum                                              | 8.6 W                                |
| apparent pick-up power of magnet coil at AC                              | 218 VA                               |
| apparent holding power of magnet coil at AC                              | 25 VA                                |
| operating range factor control supply voltage rated value of magnet coil | 0.85 ... 1.1                         |
| percentual drop-out voltage of magnet coil related to the input voltage  | 50 %                                 |
| ON-delay time                                                            | 19 ... 29 ms                         |
| OFF-delay time                                                           | 10 ... 24 ms                         |
| <b>Overload relay</b>                                                    |                                      |

|                                                                                                                               |                                                     |
|-------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|
| product function                                                                                                              |                                                     |
| • overload protection                                                                                                         | Yes                                                 |
| • phase failure detection                                                                                                     | Yes                                                 |
| • asymmetry detection                                                                                                         | Yes                                                 |
| • ground fault detection                                                                                                      | Yes                                                 |
| • test function                                                                                                               | Yes                                                 |
| • external reset                                                                                                              | Yes                                                 |
| reset function                                                                                                                | Manual, automatic and remote                        |
| trip class                                                                                                                    | CLASS 5 / 10 / 20 (factory set) / 30                |
| adjustable current response value current of the current-dependent overload release                                           | 0.75 ... 3.4 A                                      |
| make time with automatic start after power failure maximum                                                                    | 3 s                                                 |
| relative repeat accuracy                                                                                                      | 1 %                                                 |
| product feature protective coating on printed-circuit board                                                                   | Yes                                                 |
| number of NC contacts of auxiliary contacts of overload relay                                                                 | 1                                                   |
| number of NO contacts of auxiliary contacts of overload relay                                                                 | 1                                                   |
| operational current of auxiliary contacts of overload relay                                                                   |                                                     |
| • at AC at 600 V                                                                                                              | 5 A                                                 |
| • at DC at 250 V                                                                                                              | 1 A                                                 |
| contact rating of auxiliary contacts of overload relay according to UL                                                        | 5A@600VAC (B600), 1A@250VDC (R300)                  |
| insulation voltage (Ui)                                                                                                       |                                                     |
| • with single-phase operation at AC rated value                                                                               | 600 V                                               |
| • with multi-phase operation at AC rated value                                                                                | 300 V                                               |
| <b>Enclosure</b>                                                                                                              |                                                     |
| design of the housing                                                                                                         | dustproof, waterproof & resistant to corrosion      |
| <b>Mounting/wiring</b>                                                                                                        |                                                     |
| mounting position                                                                                                             | Vertical                                            |
| fastening method                                                                                                              | Surface mounting and installation                   |
| type of electrical connection for supply voltage line-side                                                                    | Screw-type terminals                                |
| tightening torque [lbf-in] for supply                                                                                         | 20 lbf-in                                           |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                             | 1x (14 ... 2 AWG)                                   |
| temperature of the conductor for supply maximum permissible                                                                   | 75 °C                                               |
| material of the conductor for supply                                                                                          | AL or CU                                            |
| type of electrical connection for load-side outgoing feeder                                                                   | Screw-type terminals                                |
| tightening torque [lbf-in] for load-side outgoing feeder                                                                      | 20 ... 24 lbf-in                                    |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded            | 2x (14 ... 10 AWG)                                  |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                                | 75 °C                                               |
| material of the conductor for load-side outgoing feeder                                                                       | CU                                                  |
| type of electrical connection of magnet coil                                                                                  | Screw-type terminals                                |
| tightening torque [lbf-in] at magnet coil                                                                                     | 5 ... 12 lbf-in                                     |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                           | 2x (16 ... 12 AWG)                                  |
| temperature of the conductor at magnet coil maximum permissible                                                               | 75 °C                                               |
| material of the conductor at magnet coil                                                                                      | CU                                                  |
| type of electrical connection for auxiliary contacts                                                                          | Screw-type terminals                                |
| tightening torque [lbf-in] at contactor for auxiliary contacts                                                                | 10 ... 15 lbf-in                                    |
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded      | 1x (12 AWG), 2x (16 ... 14 AWG), 2x (18 ... 16 AWG) |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible                                          | 75 °C                                               |
| material of the conductor at contactor for auxiliary contacts                                                                 | CU                                                  |
| type of electrical connection at overload relay for auxiliary contacts                                                        | Screw-type terminals                                |
| tightening torque [lbf-in] at overload relay for auxiliary contacts                                                           | 7 ... 10 lbf-in                                     |
| type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded | 2x (20 ... 14 AWG)                                  |
| temperature of the conductor at overload relay for auxiliary                                                                  | 75 °C                                               |

|                                                                                   |                                                     |
|-----------------------------------------------------------------------------------|-----------------------------------------------------|
| contacts maximum permissible                                                      |                                                     |
| material of the conductor at overload relay for auxiliary contacts                | CU                                                  |
| <b>Short-circuit current rating</b>                                               |                                                     |
| design of the fuse link for short-circuit protection of the main circuit required | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| design of the short-circuit trip                                                  | Thermal magnetic circuit breaker                    |
| maximum short-circuit current breaking capacity (Icu)                             |                                                     |
| • at 240 V                                                                        | 14 kA                                               |
| • at 480 V                                                                        | 10 kA                                               |
| • at 600 V                                                                        | 10 kA                                               |
| certificate of suitability                                                        | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |
| <b>Approvals Certificates</b>                                                     |                                                     |
| <b>Test Certificates</b>                                                          |                                                     |



#### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:22CUB32FF>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/US/en/ps/US2:22CUB32FF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:22CUB32FF&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:22CUB32FF&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:22CUB32FF/certificate>



last modified:

10/23/2025

