



Reversing contactor Size 1P Single phase full voltage Contactor amp rating 35Amp  
3 w 110V 50HZ / 120V 60HZ coil Non-combination type Enclosure NEMA type 1  
Indoor general purpose use Standard width enclosure

|   |                             |
|---|-----------------------------|
| product brand name  | Class 43                    |
| design of the product   | Reversing contactor         |
| special product feature   | Half-size controller        |
| <b>General technical data</b>   |                             |
| weight [lb]   | 22 lb                       |
| Height x Width x Depth [in]   | 20 × 12 × 8 in              |
| touch protection against electrical shock                               | NA for enclosed products    |
| installation altitude [ft] at height above sea level maximum            | 6560 ft                     |
| ambient temperature [°F]  |                             |
| • during storage  | -22 ... +149 °F             |
| • during operation  | -4 ... +104 °F              |
| ambient temperature   |                             |
| • during storage  | -30 ... +65 °C              |
| • during operation  | -20 ... +40 °C              |
| country of origin   | USA                         |
| <b>Horsepower ratings</b>   |                             |
| yielded mechanical performance [hp] for single-phase AC motor           |                             |
| • at 115 V rated value  | 3 hp                        |
| • at 200/208 V rated value  | 5 hp                        |
| • at 220/230 V rated value  | 5 hp                        |
| • at 460/480 V rated value  | 0 hp                        |
| • at 575/600 V rated value  | 0 hp                        |
| <b>Contactors</b>   |                             |
| size of contactor   | Controller half size 1 3/4  |
| number of NO contacts for main contacts                                 | 2                           |
| operating voltage for main current circuit at AC at 60 Hz maximum       | 240 V                       |
| operational current at AC at 600 V rated value                          | 35 A                        |
| mechanical service life (operating cycles) of the main contacts typical | 10000000                    |
| <b>Auxiliary contact</b>  |                             |
| number of NC contacts at contactor for auxiliary contacts               | 2                           |
| number of NO contacts at contactor for auxiliary contacts               | 2                           |
| number of total auxiliary contacts maximum                              | 8                           |
| contact rating of auxiliary contacts of contactor according to UL       | 345VA@115VAC / 768VA@240VAC |
| <b>Coil</b>   |                             |
| type of voltage of the control supply voltage                           | AC                          |
| control supply voltage  |                             |
| • at AC at 50 Hz rated value  | 110 V                       |

|  |              |
|--|--------------|
| • at AC at 60 Hz rated value   | 120 V        |
| holding power at AC minimum  | 8.6 W        |
| apparent pick-up power of magnet coil at AC                              | 218 VA       |
| apparent holding power of magnet coil at AC                              | 25 VA        |
| operating range factor control supply voltage rated value of magnet coil | 0.85 ... 1.1 |
| percentual drop-out voltage of magnet coil related to the input voltage  | 50 %         |
| ON-delay time  | 19 ... 29 ms |
| OFF-delay time   | 10 ... 24 ms |

#### Enclosure

|   |                                    |
|---|------------------------------------|
| degree of protection NEMA rating of the enclosure | NEMA Type 1                        |
| design of the housing                             | indoors, usable on a general basis |

#### Mounting/wiring

|  |   |
|--|---|
| mounting position  | Vertical  |
| fastening method   | Surface mounting and installation                   |
| type of electrical connection for supply voltage line-side   | Screw-type terminals                                |
| tightening torque [lbf-in] for supply  | 45 lbf-in   |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                        | 1x (14 ... 2 AWG)                                   |
| temperature of the conductor for supply maximum permissible  | 75 °C   |
| material of the conductor for supply   | AL or CU  |
| type of electrical connection for load-side outgoing feeder  | Screw-type terminals                                |
| tightening torque [lbf-in] for load-side outgoing feeder   | 45 lbf-in   |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded       | 1x (14 ... 2 AWG)                                   |
| temperature of the conductor for load-side outgoing feeder maximum permissible   | 75 °C   |
| material of the conductor for load-side outgoing feeder  | AL or CU  |
| type of electrical connection of magnet coil   | Screw-type terminals                                |
| tightening torque [lbf-in] at magnet coil  | 5 ... 12 lbf-in                                     |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                      | 2x (16 ... 12 AWG)                                  |
| temperature of the conductor at magnet coil maximum permissible  | 75 °C   |
| material of the conductor at magnet coil   | CU  |
| type of electrical connection at contactor for auxiliary contacts  | Screw-type terminals                                |
| tightening torque [lbf-in] at contactor for auxiliary contacts   | 10 ... 15 lbf-in                                    |
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded | 1x (12 AWG), 2x (16 ... 14 AWG), 2x (18 ... 16 AWG) |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible                                     | 75 °C   |
| material of the conductor at contactor for auxiliary contacts  | CU  |

#### Short-circuit current rating

|   |   |
|---|---|
| design of the fuse link for short-circuit protection of the main circuit required | 10kA@600V (Class H or K); 100kA@600V (Class R or J) |
| design of the short-circuit trip  | Thermal magnetic circuit breaker                    |
| maximum short-circuit current breaking capacity (I <sub>cu</sub> )                |   |
| • at 240 V  | 14 A  |
| • at 480 V  | 10 A  |
| • at 600 V  | 10 A  |
| certificate of suitability  | NEMA ICS 2; UL 508; CSA 22.2, No.14                 |

#### Approvals Certificates

##### Test Certificates



#### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:43EP12BF>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/US/en/ps/US2:43EP12BF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:43EP12BF&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:43EP12BF&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:43EP12BF/certificate>



| LETTER | KNOCKOUT & CONDUIT SIZE             |
|--------|-------------------------------------|
| A      | ø22.2 X ø28.6 FOR 12.7 & 19 CONDUIT |
| B      | ø43.8 X ø50 FOR 31.8 & 38.1 CONDUIT |
| C      | ø50 X ø62.7 FOR 38.1 & 50.8 CONDUIT |

last modified:

10/23/2025