



Figure similar

SIPLUS SIMOCODE pro V basic unit 2 based on 3UF7010-1AU00-0 with conformal coating, -25...+60 °C, PROFIBUS DP interface 12 Mbps, RS-485; 4 I/3 O freely parameterizable US: 110-240 V AC/DC; input for thermistor connection; monostable relay outputs; expandable by expansion modules

product brand name	SIRIUS
product designation	Motor management system
design of the product	basic unit 2
product type designation	SIMOCODE pro V PB
General technical data	
certificate of suitability	CE / RoHS
product function	- current measurement - voltage measurement - active power measurement - energy measurement - frequency measurement - bus communication - data acquisition function - diagnostics function - password protection - test function - maintenance function - MRRT redundancy procedure No No Yes No No Yes Yes Yes Yes Yes Yes No
product component	- input for thermistor connection - digital input - input for analog temperature sensors - input for ground fault detection - relay output Yes Yes No No Yes
product extension	- temperature monitoring module - current measuring module - current/voltage measuring module - fail-safe digital I/O module - ground-fault monitoring module - decoupling module - analog I/O module - digital I/O module with monostable outputs - digital I/O module with bistable outputs - control unit with display - control unit Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
apparent power consumption	8.3 VA

consumed active power	3.6 W
insulation voltage with degree of pollution 3 at AC rated value	300 V
surge voltage resistance rated value	4 000 V
shock resistance	
• according to IEC 60068-2-27	15 g / 11 ms
• vibration resistance	1 ... 6 Hz / 15 mm; 6 ... 500 Hz / 2 g
switching capacity current of the NO contacts of the relay outputs at AC-15	
• at 24 V	6 A
• at 120 V	6 A
• at 230 V	3 A
switching capacity current of the NO contacts of the relay outputs at DC-13	
• at 24 V	2 A
• at 60 V	0.55 A
• at 125 V	0.25 A
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) typical	100 000
buffering time in the event of power failure	0 s
reference code according to IEC 81346-2	F
continuous current of the NO contacts of the relay outputs	
• at 50 °C	6 A
• at 60 °C	5 A
type of input characteristic	Type 1 in accordance with EN 61131-2
Substance Prohibitance (day/month/year)	09/13/2024
SVHC substance name	Lead CAS-No. 7439-92-1
Net Weight	0.369 kg
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV (power ports) / 1 kV (signal ports)
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
• due to high-frequency radiation according to IEC 61000-4-6	10 V
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
conducted HF interference emissions according to CISPR11	corresponds to degree of severity A
field-bound HF interference emission according to CISPR11	corresponds to degree of severity A
Inputs/ Outputs	
product function	
• parameterizable inputs	Yes
• parameterizable outputs	Yes
number of inputs	4
• for thermistor connection	1
number of digital inputs with a common reference potential	4
digital input version	
• type 1 acc. to IEC 61131	Yes
input voltage at digital input at DC	
• rated value	24 V
number of outputs	3
number of semiconductor outputs	0
number of outputs as contact-affected switching element	3
switching behavior	monostable
number of relay outputs	3
type of relay outputs	Monostable

wire length for digital signals maximum	300 m
wire length for thermistor connection	
• with conductor cross-section = 0.5 mm ² maximum	50 m
• with conductor cross-section = 1.5 mm ² maximum	150 m
• with conductor cross-section = 2.5 mm ² maximum	250 m
Protective and monitoring functions	
product function	
• asymmetry detection	Yes
• blocking current evaluation	Yes
• power factor monitoring	Yes
• ground fault detection	Yes
• ground-fault monitoring	No
• phase failure detection	Yes
• phase sequence recognition	Yes
• voltage detection	Yes
• monitoring of number of start operations	Yes
• overvoltage detection	Yes
• overcurrent detection 1 phase	Yes
• undervoltage detection	Yes
• undercurrent detection 1 phase	Yes
• active power monitoring	Yes
product function	
• current detection	Yes
• overload protection	Yes
• evaluation of thermistor motor protection	Yes
total cold resistance number of sensors in series maximum	1.5 kΩ
response value of thermoresistor	3 400 ... 3 800 Ω
• of the short-circuit control	9 Ω
release value of thermoresistor	1 500 ... 1 650 Ω
Motor control functions	
product function	
• parameterizable overload relay	Yes
• circuit breaker control	Yes
• direct start	Yes
• reverse starting	Yes
• star-delta circuit	Yes
• star-delta reversing circuit	Yes
• Dahlander circuit	Yes
• Dahlander reversing circuit	Yes
• pole-changing switch circuit	Yes
• pole-changing switch reversing circuit	Yes
• slide control	Yes
• valve control	Yes
Communication/ Protocol	
protocol is supported	
• PROFIBUS DP protocol	Yes
• PROFINET IO protocol	No
• PROFIsafe protocol	Yes
• Modbus RTU	No
• EtherNet/IP	No
• OPC UA Server	No
• LLDP	No
• Address Resolution Protocol (ARP)	No
• SNMP	No
• HTTPS	No
• NTP	No
• Media Redundancy Protocol (MRP)	No
product function	
• web server	No

• shared device • at the Ethernet interface Autocrossover • at the Ethernet interface Autonegotiation • at the Ethernet interface Autosensing • is supported Device Level Ring (DLR) • is supported PROFINET system redundancy (S2) • supports PROFINET energy measured values • supports PROFINET energy shutdown	No
transfer rate maximum	12 Mbit/s
identification & maintenance function	
• I&M0 - device-specific information • I&M1 - higher level designation/location designation • I&M2 - installation date • I&M3 - comment	Yes
	Yes
	Yes
	Yes
type of electrical connection of the communication interface	9-pin SUB-D socket (12 Mbit) / screw terminal (1.5 Mbit)
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting
height	111 mm
width	45 mm
depth	124 mm
required spacing	
• top • bottom • left • right	40 mm
	40 mm
	0 mm
	0 mm
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes
type of electrical connection	
• for auxiliary and control circuit	screw-type terminals
type of connectable conductor cross-sections	
• solid • finely stranded with core end processing • for AWG cables solid • for AWG cables stranded	1x (0.5 ... 4.0mm ²), 2x (0.5 ... 2.5 mm ²)
	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²)
	1x (20 ... 12), 2x (20 ... 14)
	1x (20 ... 14), 2x (20 ... 16)
tightening torque with screw-type terminals	0.8 ... 1.2 N·m
tightening torque [lbf·in] with screw-type terminals	7 ... 10.3 lbf·in
type of connectable conductor cross-sections for PROFIBUS wire	2x 0.34 mm ² , AWG 22
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
• during operation • during storage • during transport	-25 ... +60 °C
	-40 ... +80 °C
	-40 ... +80 °C
environmental category	
• during operation according to IEC 60721 • during storage according to IEC 60721 • during transport according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
	1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4
	2K2, 2C1, 2S1, 2M2
relative humidity	
• during operation	5 ... 95 %
contact rating of auxiliary contacts according to UL	B300 / R300
Short-circuit protection	
design of short-circuit protection per output	Fuse links: gG 6 A, quick-response 10 A (IEC 60947-5-1), miniature circuit-breaker C char.: 1.6 A (IEC 60947-5-1) or 6 A (I _N < 500 A)
Electrical Safety	
touch protection against electrical shock	finger-safe

Galvanic isolation	
(electrically) protective separation according to IEC 60947-1	All circuits with protective separation (double creepage paths and clearances), the information in the "Protective Separation" test report, No. A0258, must be observed (link see further information)
design of the electrical isolation	Protective separation in accordance with IEC 60947-1 for all circuits
note	Test report No. A0258 must be observed (https://support.industry.siemens.com/cs/document/109748152)

Control circuit/ Control	
product function soft starter control	Yes
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
- at 50 Hz rated value - at 60 Hz rated value	110 ... 240 V 110 ... 240 V
control supply voltage frequency	
1 rated value 2 rated value	50 Hz 60 Hz
relative symmetrical tolerance of the control supply voltage frequency	5 %
control supply voltage at DC rated value	110 ... 240 V
operating range factor control supply voltage rated value at DC	
- initial value - full-scale value	0.85 1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
- initial value - full-scale value	0.85 1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
- initial value - full-scale value	0.85 1.1
inrush current peak	
at 240 V	15 A
duration of inrush current peak	
at 240 V	1 ms

Approvals Certificates

General Product Approval

[China RoHS](#)

[Manufacturer Declaration](#)



[China RoHS](#)



General Product Approval

EMV



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)


<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=6AG1010-1AU00-4AA0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=6AG1010-1AU00-4AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/6AG1010-1AU00-4AA0>



last modified:

4/5/2026