

SIMATIC IPC427E (Microbox PC), HD graphic onboard, 4x USB V3.0 (high current), PCIe (optional), Core i5-6442EQ; 3x Gbit Ethernet (IE/PN); Mounting onto standard rail; 8 GB and NVRAM; without RS232/485; 2x PCIe (x4 and x1); Windows 10 Enterprise 2019 LTSC (64-bit), MUI (en,de,fr,it,es), for Celeron, i3 and i5, Without replaceable mass storage; 240 GB solid-state drive SATA Without SIMATIC software; 24 V DC industrial power supply

General information	
Product type designation	IPC427E
Installation type/mounting	
Mounting	DIN rail, wall mounting, portrait mounting
Design	Box PC, built-in unit
Supply voltage	
Type of supply voltage	24 V DC
Rated value (DC)	24 V; PELV / SELV floating
Mains buffering	
• Mains/voltage failure stored energy time	20 ms
Processor	
Processor type	Celeron G3902 (2C/2T, 1.6 GHz, 2 MB Cache); Core i3-6102E (2C/4T, 1.9 GHz, 3 MB Cache); Core i5-6442EQ (4C/4T, 1.9 (2.7) GHz, 6 MB Cache, iAMT); Xeon E3-1505L v5 (4C/8T, 2.0 (2.8) GHz, 8 MB Cache, iAMT)
Chipset	Intel C236 / Intel H110
Graphic	
Graphics controller	Intel HD graphics controller
Drives	
Hard disk	2.5" SATA ≥ 320 GB
SSD	Yes; 128 / 240 / 480 GB
Storage	
Type of memory	DDR4-2400 SO-DIMM
Main memory	4 / 8 / 16 GB, ECC optional
Capacity of main memory, max.	16 Gbyte
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	512 kbyte; 128 KB can be stored in the buffer time; optional
Hardware configuration	
Slots	
• Number of PCI slots	2; Optional
• Number of compact flash slots	1; CFast
Interfaces	
Number of industrial Ethernet interfaces	3; Ethernet (2x RJ45, optional 3x RJ45)
serial interface	Without / 2x COM (RS 232 / 485 / 422; switchable)
Video interfaces	
• Graphics interface	2x DisplayPort
Industrial Ethernet	
• Industrial Ethernet interface	
— 100 Mbps	Yes
— 1000 Mbps	Yes
Interrupts/diagnostics/status information	
LED status display	1x power, 3x user
Bus diagnostics	Yes
Integrated Functions	
Monitoring functions	
• Temperature monitoring	Yes
• Fan	No

Subject to change without notice
© Copyright Siemens

eClass	12	19-20-01-02
eClass	9.1	19-20-01-02
eClass	9	19-20-01-02
eClass	8	19-20-01-02
eClass	7.1	19-20-01-02
eClass	6	19-20-01-02
ETIM	10	EC001413
ETIM	9	EC001413
ETIM	8	EC001413
ETIM	7	EC001413

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



General Product Approval

For use in hazardous locations



[BIS CRS](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)

[CCC-Ex](#)



Maritime application

Dangerous goods



[NK / Nippon Kaiji Kyokai](#)

[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

[Dangerous goods information](#)

[Test Summary Report UN 38.3](#)

Dangerous goods

Environment

[Dangerous goods information](#)

[Test Summary Report UN 38.3](#)

[Environmental Confirmations](#)

[Environmental Confirmations](#)

last modified:

6/10/2026