

Siemens
EcoTech



SIMATIC IPC BX-39A; Intel(R) UHD graphic onboard; 4x USB 3.2; Ethernet (10/100/1000); PCIe (optional) Intel Xeon W-11155MLE (1.8/3.1 GHz, 4C/8T); DIN-rail mounting; 16 GB; M.2 SSD 256 GB Eco; without 2nd mass storage: Windows 11 IoT Enterprise 2024 LTSC for Celeron Xeon W-11155MLE, Xeon W-11555MLE; without option 1; Restore stick image with D&D and software image (if selected) only via OSD (Online portal) 24 V DC industrial power supply (NAU, isolated, bridging time);

General information	
Product type designation	BX-39A
Installation type/mounting	
Mounting	DIN rail, wall mounting, portrait mounting
Design	Box PC, built-in unit
Supply voltage	
Type of supply voltage	24 V DC
Rated value (DC)	24 V
Mains buffering	
• Mains/voltage failure stored energy time	20 ms
Input current	
Current consumption (rated value)	5 A; at 24 V DC and without load
Current consumption, max.	5 A; At 24 V DC
Inrush current, max.	75 A; max. 75 A for 0.2 ms max. 9 A for further 5 ms max. 8 A for further 40 ms
Processor	
Processor type	Intel® Celeron 6600HLE (2.1 GHz, 2C/2T) Intel® Xeon W-11155MLE (1.8/3.1 GHz, 4C/8T) Intel® Xeon W-11555MLE (1.9/4.4 GHz, 6C/12T) Intel® Xeon W-11865MLE (1.5/4.5 GHz, 8C/16T)
Chipset	Intel® RM590E
Graphic	
Graphics controller	Intel® UHD Graphics 16 EUs (for Intel® Celeron® 6600HLE and Intel® Xeon® W-11155MLE) / Intel® UHD Graphics 32 EUs (for Intel® Xeon® W-11555MLE and Intel® Xeon® W-11865MLE)
Drives	
Hard disk	M.2 SSD 256 GB Eco
SSD	Yes; 256 GB Eco
Storage	
Type of memory	DDR4-3200 SO-DIMM
Main memory	4 / 8 / 16 / 32 GB; ECC optional
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	512 kbyte; 128 KB can be stored in the buffer time; optional
Hardware configuration	
Slots	
• Number of PCI slots	2
• Number of compact flash slots	0
Interfaces	
Number of industrial Ethernet interfaces	4; 4x Gigabit Ethernet (IE/PN)
serial interface	1x / 2x (optional) COM (RS 232 / 485 / 422; selectable)
Video interfaces	
• Graphics interface	2x DisplayPort (DP1.4-capable): maximum 4096 × 2304 / 60 Hz / 36 bit
Industrial Ethernet	
• Industrial Ethernet interface	
— 100 Mbps	Yes
— 1000 Mbps	Yes
Interrupts/diagnostics/status information	
LED status display	1x power, 3x user

Bus diagnostics	Yes
Integrated Functions	
Monitoring functions	
• Temperature monitoring	Yes
• Fan	No
• Monitoring function via network	Optional
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
Siemens Eco Profile (SEP)	Siemens EcoTech
CE mark	Yes
UKCA mark	Yes
CSA approval	Yes
UL approval	Yes; UL 61010-2-201 Second Edition, File E85972
• UL 508	No
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
EAC (formerly Gost-R)	Yes
FCC	Yes
BSMI	No; in preparation
BIS	Yes
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	619 kg
— global warming potential, (during production) [CO2 eq]	68.8 kg
— global warming potential, (during operation) [CO2 eq]	566 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-15.8 kg
Marine approval	
• Germanischer Lloyd (GL)	Yes
• American Bureau of Shipping (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	Yes
• Korean Register of Shipping (KRS)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (Class NK)	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	3 000 m
Relative humidity	
• Operation, max.	85 %
Vibrations	
• Vibration resistance during operation acc. to IEC 60068-2-6	tested according to IEC 60068-2-6; 5 Hz to 9 Hz: 3.5 mm; 9 Hz to 500 Hz: 9.8 m/s²
Operating systems	
pre-installed operating system	Windows 10 IoT Enterprise 2021 LTSC, Windows 11 IoT Enterprise 2024 LTSC, Industrial OS
without operating system	Yes; Optional
pre-installed operating system	
• Windows 10 Enterprise	Yes; Windows 10 IoT Enterprise 2021 LTSC

Mechanics/material					
Enclosure material (front)	Continuous-cast aluminum				
Dimensions					
Width	262 mm				
Height	139.69999 mm				
Depth	62.6 mm				
Approvals / Certificates					
General Product Approval					
 EG-Konf.		 UL	Miscellaneous	 RCM	
General Product Approval			For use in hazardous locations		
BIS CRS		 EG-Konf.		 UL	 ATEX
For use in hazardous locations		Maritime application			
 IECEX	Miscellaneous	 ABS	 BUREAU VERITAS	 DNV	 LRS
Maritime application		Dangerous goods		Environment	
NK / Nippon Kaiji Ky- okai	CCS (China Classifica- tion Society)	KR (Korean Register of Shipping)	Dangerous goods in- formation		

last modified: 6/22/2026 