

SITOP modular/3AC/24VDC/40A/CO

SITOP modular plus 40 A Stabilized power supply input: 3 AC 400-500 V output: 24 V DC/40 A Option for with protective varnish



Figure similar

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP1437-3BA00-8AA0
input	
type of the power supply network	3-phase AC
supply voltage at AC	
• minimum rated value	400 V
• maximum rated value	500 V
• initial value	320 V
• full-scale value	550 V
supply voltage at AC	Starting from $V_{in} > 340$ V
wide range input	Yes
overvoltage overload capability	$2.3 \times V_{in}$ rated, 1.3 ms
buffering time for rated value of the output current in the event of power failure minimum	6 ms
operating condition of the mains buffering	at $V_{in} = 400$ V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 400 V	2.2 A
current limitation of inrush current at 25 °C maximum	70 A
I ² t value maximum	2.8 A ² ·s
fuse protection type	none
fuse protection type in the feeder	Required: 3-pole connected miniature circuit breaker 10 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)
output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28.8 V; max. 960 W
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.2 %
residual ripple	
• maximum	100 mV
voltage peak	

• maximum	200 mV
display version for normal operation	Green LED for 24 V OK
type of signal at output	via signaling module (6EP1961-3BA10)
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	2.5 s
voltage increase time of the output voltage	
• maximum	500 ms
output current	
• rated value	40 A
• rated range	0 ... 40 A; +60 ... +70 °C: Derating 2%/K
supplied active power typical	960 W
short-term overload current	
• at short-circuit during operation typical	120 A
duration of overloading capability for excess current	
• at short-circuit during operation	25 ms
constant overload current	
• on short-circuiting during the start-up typical	46 A
bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	90 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	106 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	1 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	2 %
setting time	
• load step 50 to 100% typical	4 ms
• load step 100 to 50% typical	4 ms
setting time	
• maximum	10 ms
protection and monitoring	
design of the overvoltage protection	< 35 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Alternatively, constant current characteristic approx. 46 A or latching shutdown
• typical	46 A
enduring short circuit current RMS value	
• typical	46 A
display version for overload and short circuit	LED yellow for "overload", LED red for "latching shutdown"
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
protection class IP	IP20
EMC	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; UL-Listed (UL 508), File E197259

• UKCA marking • EAC approval • Regulatory Compliance Mark (RCM) • NEC Class 2	Yes Yes Yes No
type of certification	
• CB-certificate	No
MTBF at 40 °C	485 437 h
standards, specifications, approvals hazardous environments	
certificate of suitability	
• IECEx • ATEX • ULhazloc approval • FM registration	No No No No
standards, specifications, approvals marine classification	
shipbuilding approval	No
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Lloyds Register of Shipping (LRS)	No No No No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total • during manufacturing • during operation • after end of life	2 762.3 kg 76.5 kg 2 684.1 kg 0.64 kg
ambient conditions	
ambient temperature	
• during operation • during transport • during storage	0 ... 70 °C; with natural convection -40 ... +85 °C -40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
• at input • at output • for auxiliary contacts	L1, L2, L3, PE: 1 screw terminal each for 0.2 ... 4 mm² single-core/finely stranded +, -: 2 screw terminals each for 0.33 ... 10 mm² -
mechanical data	
width × height × depth of the enclosure	240 × 125 × 125 mm
installation width × mounting height	240 mm × 225 mm
required spacing	
• top • bottom • left • right	50 mm 50 mm 0 mm 0 mm
fastening method	Snaps onto DIN rail EN 60715 35x15
• DIN-rail mounting • S7 rail mounting • wall mounting	Yes No No
housing can be lined up	Yes
net weight	3.2 kg
accessories	
electrical accessories	Buffer module, signaling module
further information internet links	
internet link	
• to website: Industry Mall • to web page: selection aid TIA Selection Tool	https://mall.industry.siemens.com https://www.siemens.com/tstcloud

- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://siemens.com/cax>
<https://support.industry.siemens.com>

additional information

other information

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications

	Version	Classification
eClass	16	27-04-07-01
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration

• global warming potential [CO2 eq] / during manufacturing	76.5 kg
• global warming potential [CO2 eq] / during operation	2684.1 kg
• global warming potential [CO2 eq] / after end of life	0.64 kg
• global warming potential [CO2 eq] / total	2762.3 kg

Environment

General Product Approval



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



[China RoHS](#)

General Product Approval



