



SITOP Battery module/24V/7AH

SITOP battery module 24 V/7 Ah with maintenance free sealed lead-acid batteries for SITOP DC UPS module 6 A, 15 A and 40 A

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP1935-6ME21
electrical data	
end-of-charge voltage at DC	
• at -10 °C recommended	29 V
• at 0 °C recommended	28.4 V
• at 10 °C recommended	27.8 V
• at 20 °C recommended	27.3 V
• at 30 °C recommended	26.8 V
• at 40 °C recommended	26.6 V
• at 50 °C recommended	26.3 V
output	
battery capacity	7 A·h
output current in buffering mode maximum	30 A
peak current	30 A
charging current maximum	1.75 A
output voltage at DC rated value	24 V
interfaces	
communication function	No
protection and monitoring	
design of short-circuit protection	Battery fuse 20 A/32 V (solid-state circuitry blade-type fuse + support)
design of the overload protection	Valve control
safety	
operating resource protection class	Class III
protection class IP	IP00
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627
• EAC approval	Yes
standards, specifications, approvals hazardous environments	
certificate of suitability	
• ATEX	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• Det Norske Veritas (DNV)	Yes

standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO ₂ eq]	
• total • during manufacturing • during operation • after end of life	23.293 kg 12.827 kg 8.167 kg 0.676 kg
ambient conditions	
ambient condition	For storage, mounting and operation of lead-acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed. You must ensure that the battery site is sufficiently ventilated. Possible sources of ignition must be at least 50 cm away.
ambient temperature	
• during operation • during transport • during storage	-15 ... +50 °C -20 ... +50 °C -20 ... +50 °C
relative temporary capacity loss at 20 °C in a month typical	3 %
service life	
service life of energy storage	
• typical • at 20 °C typical • at 30 °C typical • at 40 °C typical • at 50 °C typical	capacity falls to 80 % of original capacity (according to EUROBAT) 4 a 2 a 1 a 0.5 a
note	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.
connection method	
type of electrical connection	spring-loaded terminals
• for UPS module	1 screw terminal each for 0.08 ... 4 mm ² for + BAT and - BAT
mechanical data	
width × height × depth of the enclosure	186 × 168 × 121 mm
installation width × mounting height	206 mm × 188 mm
fastening method	can be screwed onto flat surface (keyhole mounting for hooking in to M4 screws)
• DIN-rail mounting • S7 rail mounting • wall mounting	No No Yes
net weight	6 kg
number of cells	12
accessories	
product component included	Accessories pack with solid-state circuitry fuse 20 A and 30 A
further information internet links	
internet link	
• to website: Industry Mall • to web page: selection aid TIA Selection Tool • to web page: power supplies • to website: CAX-Download-Manager • to website: Industry Online Support	https://mall.industry.siemens.com https://www.siemens.com/tstcloud https://siemens.com/sitop https://www.siemens.com/cax https://support.industry.siemens.com
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected

to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications			
		Version	Classification
	eClass	16	27-05-04-03
	eClass	14	27-05-04-03
	eClass	12	27-05-04-03
	eClass	9.1	27-05-04-03
	eClass	9	27-05-04-03
	eClass	8	27-05-04-03
	eClass	7.1	27-05-04-03
	eClass	6	27-05-04-90
	ETIM	10	EC000357
	ETIM	9	EC000357
	ETIM	8	EC000357
	ETIM	7	EC000357
	UNSPSC	15	26-11-17-01

Approvals Certificates

General Product Approval

[Manufacturer Declaration](#)

[Declaration of Conformity](#)


EG-Konf.


UL


UR

[Miscellaneous](#)

Maritime application


ABS


DNV

Dangerous goods

[Dangerous goods information](#)

[Dangerous goods information](#)

[Transport Information](#)

Environment



last modified: 5/5/2026 