



Figure similar

SITOP PSU6200/1AC/24VDC/10A/EX

SITOP PSU6200 Ex 24 V/10 A stabilized power supply input: 120 - 240 V AC
output: 24 V DC/10 A with diagnostic interface with coated printed circuit boards

General information

Technical Product Detail Page

<https://i.siemens.com/1P6EP3334-7SC00-3AX0>

input

type of the power supply network	1-phase AC or DC
supply voltage at AC	
• minimum rated value	120 V
• maximum rated value	240 V
• initial value	85 V
• full-scale value	264 V
supply voltage at DC	110 ... 240 V
input voltage at DC	85 ... 275 V
wide range input	Yes
overvoltage overload capability	300 V AC for 30 s
buffering time for rated value of the output current in the event of power failure minimum	45 ms
operating condition of the mains buffering	at $V_{in} = 240 \text{ V}$
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 120 V	2.2 A
• at rated input voltage 240 V	1.2 A
current limitation of inrush current at 25 °C maximum	6 A
fuse protection type	5 A
fuse protection type in the feeder	Circuit breaker from 4 A characteristic C/6 A characteristic B to 10 A characteristic C or circuit breaker 3RV2011-1EA10 (setting 4 A) or 3RV2711-1ED10 (UL 489)

output

voltage curve at output	Controlled, isolated DC voltage
number of outputs	1
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28 V; max. 240 W (288 W up to 45°C)
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	0.1 %
residual ripple	

• maximum	30 mV
• typical	20 mV
voltage peak	
• maximum	30 mV
• typical	20 mV
display version for normal operation	Green LED for 24 V OK
type of signal at output	Electronic contact (NO contact, contact rating 30 V DC/0.1 A) for DC O.K. or diagnostic interface
behavior of the output voltage when switching on	Overshoot of Vout < 2 %
response delay maximum	0.5 s
voltage increase time of the output voltage	
• typical	200 ms
output current	
• rated value	10 A
• rated range	0 ... 10 A; 12 A up to +45°C; +60 ... +70 °C: Derating 3%/K
supplied active power typical	240 W
short-term overload current	
• on short-circuiting during the start-up typical	12 A
• at short-circuit during operation typical	12 A
parallel switching of outputs	can be set with DIP switch
bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	92.8 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	18 W
• during no-load operation maximum	2.2 W
closed-loop control	
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	2 %
setting time	
• load step 10 to 90% typical	2 ms
• load step 90 to 10% typical	2 ms
• maximum	3 ms
protection and monitoring	
design of the overvoltage protection	< 32 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Shutdown and periodic restart attempts
• typical	12 A
overcurrent overload capability	
• in normal operation	overload capability 150 % Iout rated up to 5 s/min
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
• maximum	3.5 mA
protection class IP	IP20
EMC	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259

• UKCA marking • EAC approval • Regulatory Compliance Mark (RCM) • NEC Class 2	Yes Yes Yes No
type of certification • BIS • CB-certificate	Yes; R-41188271 Yes
standards, specifications, approvals hazardous environments	
certificate of suitability • IECEx • ATEX • ULhazloc approval • UKEX • CCC for hazardous zone according to GB standard • FM registration	Yes; IECEx Ex ec nC IIC T3 Gc Yes; ATEX (EX) II 3G Ex ec nC IIC T3 Gc Yes Yes Yes No
standards, specifications, approvals marine classification	
shipbuilding approval • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Lloyds Register of Shipping (LRS)	Yes No Yes No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration • global warming potential [CO2 eq] • total • during manufacturing • during operation • after end of life	Yes 479.5 kg 23.1 kg 455.6 kg 0.38 kg
ambient conditions	
ambient temperature • during operation • during transport • during storage	-30 ... +70 °C; with natural convection a monotonically increasing start-up from -25 °C, safe start-up from -40 °C -40 ... +85 °C -40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection • at input • at output • for auxiliary contacts	push-in terminals L1/+, L2/N/-, PE: push-in for 0.5 ... 4 mm² single-core/finely stranded +1, +2, -1, -2, -3: push-in for 0.5 ... 2.5 mm² 13, 14 (alarm signal): 1 push-in terminal each for 0.2 ... 1.5 mm²
mechanical data	
width × height × depth of the enclosure	45 × 135 × 125 mm
installation width × mounting height	45 mm × 225 mm
required spacing • top • bottom • left • right	45 mm 45 mm 0 mm 0 mm
fastening method • DIN-rail mounting • S7 rail mounting • wall mounting	Snaps onto DIN rail EN 60715 35x7.5/15 Yes No No
housing can be lined up	Yes
net weight	0.9 kg
accessories	
electrical accessories	Buffer module, redundancy module
mechanical accessories	Identification labels SIMATIC ET 200SP 6ES7193-6LF30-0AW0
further information internet links	

internet link	• to website: Industry Mall https://mall.industry.siemens.com • to web page: selection aid TIA Selection Tool https://www.siemens.com/tstcloud • to web page: power supplies https://siemens.com/sitop • to website: CAX-Download-Manager https://siemens.com/cax • to website: Industry Online Support https://support.industry.siemens.com
identification link	Yes; acc. to IEC 61406-1:2022
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)

Classifications			
		Version	Classification
	eClass	16	27-04-07-01
	eClass	14	27-04-07-01
	eClass	12	27-04-07-01
	eClass	9.1	27-04-07-01
	eClass	9	27-04-07-01
	eClass	8	27-04-90-02
	eClass	7.1	27-04-90-02
	eClass	6	27-04-90-02
	ETIM	10	EC002540
	ETIM	9	EC002540
	ETIM	8	EC002540
	ETIM	7	EC002540
	IDEA	4	4130
	UNSPSC	15	39-12-10-04

Approvals Certificates	
Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing • global warming potential [CO2 eq] / during operation • global warming potential [CO2 eq] / after end of life • global warming potential [CO2 eq] / total	23.1 kg 455.6 kg 0.38 kg 479.5 kg
Environment	General Product Approval



[Manufacturer Declaration](#)



[China RoHS](#)

General Product Approval	For use in hazardous locations
--------------------------	--------------------------------



[BIS CRS](#)



[Miscellaneous](#)



For use in hazardous locations

Maritime application

[CCC-Ex](#)



last modified:

5/5/2026