




SITOP BAT1600/Battery module/24V/38AH

SITOP BAT1600 24 V DC 38 Ah Pb battery module with maintenance- free closed lead-acid battery for SITOP UPS1600

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP4137-0GE00-0AY0
electrical data	
end-of-charge voltage at DC	
• at -10 °C recommended	28 V
• at 0 °C recommended	28 V
• at 10 °C recommended	27.8 V
• at 20 °C recommended	27.3 V
• at 30 °C recommended	26.8 V
• at 40 °C recommended	26.6 V
• at 50 °C recommended	26.3 V
output	
battery capacity	38 A·h
output current rated value	40 A
output current in buffering mode maximum	40 A
peak current	120 A; for 30 ms
charging current maximum	9 A
output voltage at DC rated value	24 V
interfaces	
communication function	Yes
protection and monitoring	
design of short-circuit protection	50A / 32V Maxi flat fuse
design of the overload protection	Valve control
display version for normal operation	Three-color: green = Buffer ready; yellow = Buffer endangered; red = Buffer not possible
safety	
operating resource protection class	Class III
protection class IP	IP20
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 61010-1, UL61010-2-201 , CSA C22.2 No. 61010-1, CSA C22.2 NO 61010-2-201), File E143289
• UKCA marking	Yes
type of certification CB-certificate	Yes
standards, specifications, approvals hazardous environments	
certificate of suitability	
• ATEX	No
standards, specifications, approvals marine classification	

shipbuilding approval	Yes
Marine classification association	
- American Bureau of Shipping Europe Ltd. (ABS) - Det Norske Veritas (DNV)	Yes in preparation
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO ₂ eq]	
- total - during manufacturing - during operation - after end of life	82.936 kg 68.81999 kg 1.778 kg 3.627 kg
ambient conditions	
ambient condition	For storage, mounting and operation of batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed.
ambient temperature	
- during operation - during transport - during storage	-15 ... +50 °C -30 ... +70 °C -20 ... +40 °C
relative temporary capacity loss at 20 °C in a month typical	3 %
service life	
service life of energy storage	
- typical - at 20 °C typical - at 30 °C typical - at 40 °C typical - at 50 °C typical	capacity falls to 80 % of original capacity (according to EUROBAT) 10 a 5 a 2.5 a 1.25 a
note	In addition to the storage temperature, additional factors, such as storage duration and charging status during storage, have a major impact on the potential service life. This means batteries should preferably be stored fully charged for short periods of time in a dry, cool and frost-proof (temperature range 0 to +20 °C) location.
connection method	
type of electrical connection	Plug-in terminals with screwed connection
- for UPS module - for control circuit and status message	1 screw terminal each for 0.5 ... 16 mm ² for + BAT and - BAT 1 screw terminal each for 0.2 ... 2.5 mm ²
mechanical data	
width × height × depth of the enclosure	394 × 212 × 165 mm
installation width × mounting height	330 mm × 262 mm
required spacing	
- top - bottom - left - right	50 mm 50 mm 0 mm 0 mm
fastening method	Floor mounting
- DIN-rail mounting - S7 rail mounting - wall mounting	No No No
net weight	27.9 kg
number of cells	2
accessories	
product component included	2x Maxi Fuse 50 A/32 V
further information internet links	
internet link	
- to website: Industry Mall - to web page: selection aid TIA Selection Tool - to web page: power supplies - to website: CAX-Download-Manager - to website: Industry Online Support	https://mall.industry.siemens.com https://www.siemens.com/tstcloud https://siemens.com/sitop https://www.siemens.com/cax https://support.industry.siemens.com
additional information	

other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
-------------------	---

security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)

Classifications			
		Version	Classification
	eClass	16	27-05-04-03
	eClass	14	27-05-04-03
	eClass	12	27-05-04-03
	eClass	9.1	27-05-04-03
	eClass	9	27-05-04-03
	eClass	8	27-05-04-03
	eClass	7.1	27-05-04-03
	eClass	6	27-05-04-90
	ETIM	10	EC000357
	ETIM	9	EC000357
	ETIM	8	EC000357
	ETIM	7	EC000357

Approvals Certificates	
General Product Approval	Dangerous goods



[Manufacturer Declaration](#)



EG-Konf.



[Dangerous goods information](#)

Dangerous goods	Environment
Dangerous goods information	Transport Information

last modified:

5/5/2026