

Control Power Transformer, 250va, PRI 208/277v, SEC 120v, Domestic,



product brand name	Control Power Transformer
design of the product	Control power voltage
special product feature	Robust design
General technical data	
weight [lb]	10 lb
Height x Width x Depth [in]	4.47 × 4.5 × 4.78 in
ambient temperature [°F] during operation	-4 ... +104 °F
ambient temperature during operation	-20 ... +40 °C
country of origin	Mexico
operating apparent power rated value	250 VA
Enclosure	
design of the housing	Open
Mounting/wiring	
mounting position	Any
fastening method	Surface mounting
type of electrical connection at output for main current circuit	Screw-type terminals (touchsafe)
type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)
Inputs/ Outputs	
input variables of primary voltage	208/277vac
output dimensions of secondary voltage	120vac
phase number of the inputs	1
electrical input frequency	50 ... 60 Hz
input voltage _1	208 V
input voltage _2	277 V
phase number of the outputs	1
electrical output frequency	60 ... 50 Hz
output voltage _1 rated value	120 V
certificate of suitability	UL / CSA
Approvals Certificates	
Test Certificates	



Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)
www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:MT0250F>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT0250F>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:MT0250F&lang=en

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT0250F/certificate>

last modified:

10/23/2025 