



SIMATIC ET 200SP, digital output module, DQ 4x 24VDC/2A High Feature, suitable for BU type A0, Color code CC02, channel diagnostics

General information	
Product type designation	DQ 4x DC 24 V/2 A HF
HW functional status	FS20 or higher
Firmware version	V2.0.3
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC02
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes; 250 µs
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V13 SP1 / -
• STEP 7 configurable/integrated from version	V5.5 / -
• PROFIBUS from GSD version/GSD revision	GSD Revision 5
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	28 mA
Current consumption, max.	28 mA
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Address space per module, max.	4 byte; 2 channels per submodule + QI information
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes

• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0
• 3-wire connection	BU type A0 with AUX terminals or potential distributor module
• 4-wire connection	BU type A0 + Potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	4
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
output type acc. to IEC 61131, type 2	Yes
Short-circuit protection	Yes; Electronic
• Response threshold, typ.	2.8 to 5.2 A
Limitation of inductive shutdown voltage to	L+ -(37 to 41V)
Controlling a digital input	Yes; Minimum current consumption 7 mA
Switching capacity of the outputs	
• with resistive load, max.	2 A
• on lamp load, max.	10 W
Load resistance range	
• lower limit	12 Ω
• upper limit	3 400 Ω
Output current	
• for signal "1" rated value	2 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", typ.	50 μ s
• "1" to "0", typ.	100 μ s
Parallel switching of two outputs	
• for uprating	No
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	2 A
• Current per module, max.	8 A
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	8 A
— up to 50 °C, max.	6 A
— up to 60 °C, max.	4 A
vertical installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	6 A
— up to 50 °C, max.	4 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Isochronous mode	
Bus cycle time (TDP), min.	500 μ s
Jitter, max.	8 μ s
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	

• Monitoring the supply voltage • Wire break • Short-circuit to ground • Short-circuit to L+ • Group error	Yes Yes; channel by channel Yes; channel by channel Yes; channel by channel Yes																														
Diagnostics indication LED																															
• Monitoring of the supply voltage (PWR-LED) • Channel status display • for channel diagnostics • for module diagnostics	Yes; green PWR LED Yes; green LED Yes; red LED Yes; green/red DIAG LED																														
Potential separation																															
Potential separation channels																															
• between the channels • between the channels and backplane bus	No Yes																														
Isolation																															
Isolation tested with	707 V DC (type test)																														
Standards, approvals, certificates																															
Suitable for safety functions	No																														
Suitable for safety-related tripping of standard modules	Yes; see FAQ Entry ID: 39198632																														
Ecological footprint																															
• environmental product declaration	Yes; type II acc. to ISO 14021																														
Global warming potential																															
— global warming potential, (total) [CO2 eq] — global warming potential, (during production) [CO2 eq] — global warming potential, (during operation) [CO2 eq] — global warming potential, (after end of life cycle) [CO2 eq]	29.3 kg 4 kg 25.6 kg 0.245 kg																														
Highest safety class achievable in safety mode																															
• Performance level according to ISO 13849-1 • SIL acc. to IEC 61508	PL d SIL 2																														
Ambient conditions																															
Ambient temperature during operation																															
• horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max.	-30 °C; < 0 °C as of FS06 60 °C -30 °C; < 0 °C as of FS06 50 °C																														
Altitude during operation relating to sea level																															
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual																														
Dimensions																															
Width	15 mm																														
Height	73 mm																														
Depth	58 mm																														
Weights																															
Weight, approx.	30 g																														
Classifications																															
	<table><tr><td></td><td>Version</td><td>Classification</td></tr><tr><td>eClass</td><td>16</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>14</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-04</td></tr><tr><td>ETIM</td><td>10</td><td>EC001599</td></tr></table>		Version	Classification	eClass	16	27-24-26-04	eClass	14	27-24-26-04	eClass	12	27-24-26-04	eClass	9.1	27-24-26-04	eClass	9	27-24-26-04	eClass	8	27-24-26-04	eClass	7.1	27-24-26-04	eClass	6	27-24-26-04	ETIM	10	EC001599
	Version	Classification																													
eClass	16	27-24-26-04																													
eClass	14	27-24-26-04																													
eClass	12	27-24-26-04																													
eClass	9.1	27-24-26-04																													
eClass	9	27-24-26-04																													
eClass	8	27-24-26-04																													
eClass	7.1	27-24-26-04																													
eClass	6	27-24-26-04																													
ETIM	10	EC001599																													

ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)

[Declaration of Conformity](#)


[Miscellaneous](#)

Maritime application

Dangerous goods

Environment



[Dangerous goods information](#)
[Dangerous goods information](#)
[Transport Information](#)


last modified:

10/23/2025 