

Siemens
EcoTech



SIMATIC ET 200SP, digital output module, DQ 4x 24 V DC/2 A High Speed, Pack quantity: 1 unit suitable for BU type A0, Color code CC00, 3 alternative operating modes: DQ, Oversampling, PWM Module diagnostics

General information	
Product type designation	DQ 4x24 V DC/2 A HS
HW functional status	From FS05
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes; Operating modes DQ and OVS only
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V15.1 or higher
• STEP 7 configurable/integrated from version	via GSD as of V5.6 HF4
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.33
Operating mode	
• DQ	Yes
• DQ with energy-saving function	Yes; Valve control
• PWM	Yes
• Cam control (switching at comparison values)	Yes; Via MtM (module-to-module communication)
• Oversampling	Yes
• MSO	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	50 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	2.5 W; at 24 V, 25 °C, DQ mode, 2 A per channel
Address area	
Address space per module	
• Inputs	1 byte; Max. 14 bytes in the cam control operating mode

• Outputs	1 byte; Max. 16 bytes in the oversampling operating mode
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type A0
• 3-wire connection	BU type A0 with AUX terminals or potential distributor module
• 4-wire connection	BU type A0 + Potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	4
Current-sinking	No
Current-sourcing	Yes; Push-pull output
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes
• Response threshold, typ.	6 A
Limitation of inductive shutdown voltage to	M (-1 V)
Controlling a digital input	No
Digital output functions, parameterizable	
• Switching tripped by comparison values	Yes
— Number of cam tracks, max.	4
— Number of cams per module, max.	16
— Number of cams per track, max.	16
— Supported axis types	Linear axes and rotary axes with modulo function
— Hysteresis	Yes
— Pulsed cam output	Yes
— Range of values for comparison values, max.	-2,147,483,648 to 2,147,483,647 (user-specific within this range)
• Freely usable digital output	Yes
• PWM output	Yes
— Number, max.	4
— Cycle duration, parameterizable	Yes; 0 ms, 0.2 ms, 0.4 ms, 0.93 ms, 1.33 ms, 4.27 ms, 10.67 ms, 21.33 ms, 34.13 ms, 59.73 ms
— Resolution of the duty cycle	0.1 %
• Digital output with oversampling	Yes
— Number, max.	4
— Values per cycle, max.	32
— Resolution, min.	100 µs
Switching capacity of the outputs	
• with resistive load, max.	2 A
• on lamp load, max.	10 W
Load resistance range	
• lower limit	12 Ω
• upper limit	3 400 Ω
Output current	
• for signal "1" rated value	2 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", max.	1 µs
• "1" to "0", max.	1 µs
Parallel switching of two outputs	
• for uprating	No
Switching frequency	
• with resistive load, max.	5 kHz
• with inductive load, max.	5 kHz
• on lamp load, max.	5 kHz
Total current of the outputs	
• Current per channel, max.	2 A
• Current per module, max.	8 A

Total current of the outputs (per module)	
horizontal installation	
— up to 30 °C, max.	8 A; DQ mode
— up to 40 °C, max.	6.9 A; DQ mode
— up to 50 °C, max.	4.7 A; DQ mode
— up to 60 °C, max.	2.5 A; DQ mode
vertical installation	
— up to 30 °C, max.	7.2 A; DQ mode
— up to 40 °C, max.	5.6 A; DQ mode
— up to 50 °C, max.	4 A; DQ mode
Cable length	
• shielded, max.	50 m
• unshielded, max.	50 m
Isochronous mode	
Execution and activation time (TCO), min.	40 µs
Bus cycle time (TDP), min.	125 µs
Jitter, max.	1 µs
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes
• Wire break	No
• short-circuit	Yes; module-wise
• Group error	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	No
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for safety functions	No
Suitable for safety-related tripping of standard modules	No
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	29.3 kg
— global warming potential, (during production) [CO2 eq]	3.98 kg
— global warming potential, (during operation) [CO2 eq]	25.6 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.245 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	

• Installation altitude above sea level, max.		5 000 m; Restrictions for installation altitudes > 2 000 m, see manual			
Absolute humidity					
• dew point, min.		-60 °C; suitable for dry room applications			
Dimensions					
Width	15 mm				
Height	73 mm				
Depth	58 mm				
Weights					
Weight, approx.	31 g				
Classifications					
		Version	Classification		
	eClass	16	27-24-26-04		
	eClass	14	27-24-26-04		
	eClass	12	27-24-26-04		
	eClass	9.1	27-24-26-04		
	eClass	9	27-24-26-04		
	eClass	8	27-24-26-04		
	eClass	7.1	27-24-26-04		
	eClass	6	27-24-26-04		
	ETIM	10	EC001599		
	ETIM	9	EC001599		
	ETIM	8	EC001599		
	ETIM	7	EC001599		
	IDEA	4	3566		
	UNSPSC	15	32-15-17-05		
Approvals / Certificates					
General Product Approval					
Miscellaneous			Manufacturer Declaration		
General Product Approval					For use in hazardous locations
		China RoHS			
For use in hazardous locations					
CCC-Ex	FM			Miscellaneous	Type Examination Certificate
For use in hazardous locations		Maritime application			
CCC-Ex					NK / Nippon Kaiji Kyokai
Maritime application			Environment		



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



last modified:

3/10/2026