

Siemens
EcoTech



SIMATIC ET 200SP, digital output module, DQ 4x24 V DC/2 A high feature, source output (PNP,sourcing output) packing unit: 1 unit, suitable for BU type A0, color code CC02, channel diagnostics for: short-circuit and wire break, supply voltage, channel fault LED

General information	
Product type designation	DQ 4x24VDC/2A HF
HW functional status	01
Firmware version	V1.0
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC02
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes; 250 µs
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	as of TIA Portal V19 with HSP0426 / integrated as of TIA Portal V20
• STEP 7 configurable/integrated from version	as of STEP 7 V5.5 SP3 with HSP0230 V11.0 / integrated as of STEP 7 V5.7 SP3
• PROFIBUS from GSD version/GSD revision	GSD Revision 5
• PROFINET from GSD version/GSD revision	GSDML V2.43
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	20 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Address space per module, max.	4 byte; 2 channels per submodule + QI information

Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Submodules	
• Number of configurable submodules, max.	2
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0
• 3-wire connection	BU type A0 with AUX terminals or potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	4
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
output type acc. to IEC 61131, type 2	Yes
Short-circuit protection	Yes; Electronic
• Response threshold, typ.	2.8 to 5.2 A
Open-circuit detection	Yes
Limitation of inductive shutdown voltage to	Typ. L+ (-50 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	2 A
• with inductive load, max.	2 A
• on lamp load, max.	10 W
Load resistance range	
• lower limit	12 Ω
• upper limit	3 400 Ω
Output current	
• for signal "1" rated value	2 A
• for signal "1" permissible range, max.	2 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", typ.	50 μs
• "1" to "0", typ.	100 μs
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	0.1 Hz; higher frequencies are possible, see Equipment Manual "Maximum permitted switching frequency of inductive loads"
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	2 A
• Current per module, max.	8 A; see Equipment Manual "Derating curve"
Total current of the outputs (per module)	
horizontal installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	8 A
— up to 50 °C, max.	6 A
— up to 60 °C, max.	4 A
vertical installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	6 A
— up to 50 °C, max.	4 A
Cable length	
• shielded, max.	1 000 m

• unshielded, max.	600 m
Isochronous mode	
Execution and activation time (TCO), min.	75 µs
Bus cycle time (TDP), min.	500 µs
Jitter, max.	8 µs
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
— parameterizable	Yes
• Wire break	Yes; channel by channel
• Short-circuit to ground	Yes; channel by channel
• Short-circuit to L+	Yes; channel by channel
• Group error	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• Between the channels and load voltage L+	No
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for safety functions	No
Suitable for safety-related tripping of standard modules	Yes; see FAQ Entry ID: 39198632
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	29.3 kg
— global warming potential, (during production) [CO2 eq]	3.98 kg
— global warming potential, (during operation) [CO2 eq]	25.6 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.245 kg
Highest safety class achievable for safety-related tripping of standard modules	
• Performance level according to ISO 13849-1	PL d
• Category according to ISO 13849-1	Cat. 3
• SIL acc. to IEC 62061	SIL 2
• remark on safety-oriented shutdown	https://support.industry.siemens.com/cs/de/en/view/39198632
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual
Absolute humidity	
• dew point, min.	-60 °C; suitable for dry room applications
Dimensions	
Width	15 mm

Height	73 mm
Depth	58 mm
Weights	
Weight, approx.	30 g
Classifications	

	Version	Classification
eClass	16	27-24-26-04
eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	10	EC001599
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Miscellaneous](#)



General Product Approval

EMV

For use in hazardous locations



[China RoHS](#)



For use in hazardous locations

[FM](#)

[CCC-Ex](#)



[Type Examination Certificate](#)



[Miscellaneous](#)

For use in hazardous locations

Maritime application

[CCC-Ex](#)



[NK / Nippon Kaiji Kyokai](#)

Maritime application

Environment



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



last modified:

2/1/2026

