



SIMATIC ET 200SP, Relay module, RQ NO 4x 120V DC..230VAC/5A ST. 4 normally open contacts, isolated contacts, packing unit: 10 pieces, fits to BU-type B0 and B1, Colour Code CC40, substitute value output, module diagnostics for: supply voltage

General information	
Product type designation	RQ 4x120 VDC ... 230 VAC/5 A NO ST
HW functional status	From FS02
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type B0, B1
Color code for module-specific color-coded label	CC40
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14
• STEP 7 configurable/integrated from version	V5.5 SP3
• PCS 7 configurable/integrated from version	V8.1 SP1
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Redundancy	
• Redundancy capability	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	55 mA; without load
Output voltage	
Rated value (AC)	230 V
Power loss	
Power loss, typ.	1.5 W
Address area	
Address space per module	
• Inputs	+ 1 byte for QI information
• Outputs	1 byte

Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type C
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type B1
• 3-wire connection	BU type B0
Digital outputs	
Type of digital output	Relays
Number of digital outputs	4
Current-sinking	Yes
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	No
Parallel switching of two outputs	
• for logic links	Yes
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	2 Hz
• with inductive load, max.	0.5 Hz
• on lamp load, max.	2 Hz
Total current of the outputs	
• Current per channel, max.	5 A
• Current per module, max.	20 A
Total current of the outputs (per module)	
horizontal installation	
— up to 50 °C, max.	20 A
— up to 60 °C, max.	16 A
vertical installation	
— up to 40 °C, max.	20 A
— up to 50 °C, max.	16 A
Relay outputs	
• Number of relay outputs	4
• Rated supply voltage of relay coil L+ (DC)	24 V
• Current consumption of relays (coil current of all relays), max.	40 mA
• external protection for relay outputs	Yes, with 6A
• Number of operating cycles, max.	7 000 000; see additional description in the manual
Switching capacity of contacts	
— with inductive load, max.	2 A; see additional description in the manual
— with resistive load, max.	5 A; see additional description in the manual
— Thermal continuous current, max.	5 A; Max. 1 385 VA, 150 W
— Switching current, min.	100 mA; 5 V DC
— Rated switching voltage (DC)	24 V DC to 120 V DC
— Rated switching voltage (AC)	24V AC to 230V AC
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	200 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire break	No
• Short-circuit	No
Diagnostics indication LED	

• Monitoring of the supply voltage (PWR-LED) • Channel status display • for channel diagnostics • for module diagnostics	Yes; green PWR LED Yes; green LED No Yes; green/red DIAG LED																																							
Potential separation																																								
Potential separation channels																																								
• between the channels	Yes																																							
• between the channels and backplane bus	Yes																																							
• between the channels and the power supply of the electronics	Yes																																							
Permissible potential difference																																								
between channels and backplane bus/supply voltage	240 V AC																																							
Isolation																																								
Isolation tested with	2 500 V DC (type test)																																							
tested with																																								
• between channels and backplane bus/supply voltage	2 500 V DC																																							
• between backplane bus and supply voltage	707 V DC (type test)																																							
Standards, approvals, certificates																																								
Suitable for safety functions	No																																							
Ecological footprint																																								
• environmental product declaration	Yes																																							
Global warming potential																																								
— global warming potential, (total) [CO2 eq]	25.5 kg																																							
— global warming potential, (during production) [CO2 eq]	3.54 kg																																							
— global warming potential, (during operation) [CO2 eq]	22.1 kg																																							
— global warming potential, (after end of life cycle) [CO2 eq]	-0.137 kg																																							
Ambient conditions																																								
Ambient temperature during operation																																								
• horizontal installation, min.	-30 °C																																							
• horizontal installation, max.	60 °C																																							
• vertical installation, min.	-30 °C																																							
• vertical installation, max.	50 °C																																							
Altitude during operation relating to sea level																																								
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m																																							
Dimensions																																								
Width	20 mm																																							
Height	73 mm																																							
Depth	58 mm																																							
Weights																																								
Weight, approx.	40 g																																							
Classifications																																								
	<table><tr><th></th><th>Version</th><th>Classification</th></tr><tr><td>eClass</td><td>16</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>14</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>12</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>9</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>8</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>7.1</td><td>27-24-26-04</td></tr><tr><td>eClass</td><td>6</td><td>27-24-26-04</td></tr><tr><td>ETIM</td><td>10</td><td>EC001599</td></tr><tr><td>ETIM</td><td>9</td><td>EC001599</td></tr><tr><td>ETIM</td><td>8</td><td>EC001599</td></tr><tr><td>ETIM</td><td>7</td><td>EC001599</td></tr></table>		Version	Classification	eClass	16	27-24-26-04	eClass	14	27-24-26-04	eClass	12	27-24-26-04	eClass	9.1	27-24-26-04	eClass	9	27-24-26-04	eClass	8	27-24-26-04	eClass	7.1	27-24-26-04	eClass	6	27-24-26-04	ETIM	10	EC001599	ETIM	9	EC001599	ETIM	8	EC001599	ETIM	7	EC001599
	Version	Classification																																						
eClass	16	27-24-26-04																																						
eClass	14	27-24-26-04																																						
eClass	12	27-24-26-04																																						
eClass	9.1	27-24-26-04																																						
eClass	9	27-24-26-04																																						
eClass	8	27-24-26-04																																						
eClass	7.1	27-24-26-04																																						
eClass	6	27-24-26-04																																						
ETIM	10	EC001599																																						
ETIM	9	EC001599																																						
ETIM	8	EC001599																																						
ETIM	7	EC001599																																						

IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Miscellaneous](#)



[Manufacturer Declaration](#)



General Product Approval

Maritime application

Environment

[China RoHS](#)



last modified:

10/23/2025