

MEF EMC-FILTER 1-PHASE 1-STAGE

I:10A U:250 VAC/300 VDC snap on

Art.No.: 10415

Country of origin: IT



Model designation: MEF 1/1 10A T

Current: 10 A

DIN-rail mountable

for universal applications

Attenuation curves on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MEF 1/1 10A T

Commercial data

URL Webshop

<https://shop.murrelektronik.com/10415>

GTIN	4048879029407
ECLASS-7.0	27420290
ECLASS-7.1	27420290
ECLASS-8.0	27420290
ECLASS-8.1	27420290
ECLASS-9.0	27420290
ECLASS-9.1	27420290
ECLASS-10.0.1	27420290
ECLASS-10.1	27420290
ECLASS-11.0	27420290
ECLASS-11.1	27420290
ECLASS-12.0	27420290
ECLASS-13.0	27420290
ECLASS-14.0	27420290
ETIM-5.0	EC002498
ETIM-6.0	EC002498
ETIM-7.0	EC002498
ETIM-8.0	EC002498
customs tariff number	85363010
EAN	4048879029407
Packaging unit	1

Electrical data

Leakage current max.	5 mA @ 250 V AC, 50 Hz
----------------------	------------------------

Electrical data | Supply

Power frequency	50 ... 60 Hz
Operating voltage AC max.	250 V
Operating voltage DC max.	300 V

Electrical data | Output

Overload current	18× (IN t) max. 0.5 ms; 1.5× (IN t) max. 1 min. (1× per hour)
------------------	---

Installation

Connection cross-section solid min.	0,2 mm ²
Connection cross-section solid max.	6 mm ²
Connection cross-section stranded/fine-stranded min.	0,2 mm ²
Connection cross-section stranded/fine-stranded max.	4 mm ²
AWG number solid min.	24
AWG number solid max.	9
AWG number stranded/fine stranded min.	24
AWG number stranded/fine stranded max.	11

Device protection | Electrical

Insulation test voltage L-N	2,7 kV
Insulation test voltage L-L	2,1 kV
Duration insulation test voltage	2 s

Mechanical data | Mounting data

Height	107 mm
Width	56 mm
Depth	39 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Climatic category (EN IEC 60068-1)	25/085/21
------------------------------------	-----------

Connection type 3	
Family construction form	terminal
No. of poles	1
Color contact carrier	yellow
Connection	Screw terminals SK
PIN 1	PE
Family construction form	terminal
No. of poles	2
Color contact carrier	gray
Connection	Screw terminals SK
PIN 1	L
PIN 2	N
Family construction form	terminal
No. of poles	2
Color contact carrier	gray
Connection	Screw terminals SK
PIN 1	L'
PIN 2	N'