



SIMATIC ET 200SP, Analog input module, AI 4xTC High Speed, suitable for BU type A0, A1, Color code CC00, channel diagnostics, 16 bit, +/-0.1%

General information	
Product type designation	AI 4xTC HS
HW functional status	From FS02
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color-coded label	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Measuring range scalable	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V15 with HSP 265/integrated as of V15.1
• STEP 7 configurable/integrated from version	V5.5 SP3 or higher
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• Oversampling	No
• MSI	Yes
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	37 mA
Current consumption, max.	50 mA
Power loss	
Power loss, typ.	0.9 W
Address area	
Address space per module	
• Address space per module, max.	16 byte; + 1 byte for QI information
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A

Selection of BaseUnit for connection variants	
• 2-wire connection	BU type A0, A1
Analog inputs	
Number of analog inputs	4
permissible input voltage for voltage input (destruction limit), max.	30 V
Cycle time (all channels), min.	5 ms; Sum of the basic conversion times and additional processing times (depending on the parameterization of the active channels)
Technical unit for temperature measurement adjustable	Yes; °C/°F/K
Input ranges (rated values), voltages	
• -1 V to +1 V — Input resistance (-1 V to +1 V)	Yes; 16 bit incl. sign 1 MΩ
• -250 mV to +250 mV — Input resistance (-250 mV to +250 mV)	Yes; 16 bit incl. sign 1 MΩ
• -50 mV to +50 mV — Input resistance (-50 mV to +50 mV)	Yes; 16 bit incl. sign 1 MΩ
• -80 mV to +80 mV — Input resistance (-80 mV to +80 mV)	Yes; 16 bit incl. sign 1 MΩ
Input ranges (rated values), thermocouples	
• type B — Input resistance (Type B)	Yes; 16 bit incl. sign 1 MΩ
• type C — Input resistance (Type C)	Yes; 16 bit incl. sign 1 MΩ
• Type E — Input resistance (Type E)	Yes; 16 bit incl. sign 1 MΩ
• Type J — Input resistance (type J)	Yes; 16 bit incl. sign 1 MΩ
• Type K — Input resistance (Type K)	Yes; 16 bit incl. sign 1 MΩ
• Type L — Input resistance (Type L)	Yes; 16 bit incl. sign 1 MΩ
• Type N — Input resistance (Type N)	Yes; 16 bit incl. sign 1 MΩ
• Type R — Input resistance (Type R)	Yes; 16 bit incl. sign 1 MΩ
• Type S — Input resistance (Type S)	Yes; 16 bit incl. sign 1 MΩ
• Type T — Input resistance (Type T)	Yes; 16 bit incl. sign 1 MΩ
• Type U — Input resistance (Type U)	Yes; 16 bit incl. sign 1 MΩ
• Type TXK/TXK(L) to GOST — Input resistance (Type TXK/TXK(L) to GOST)	Yes; 16 bit incl. sign 1 MΩ
Thermocouple (TC)	
Temperature compensation	
— Parameterizable	Yes
— Reference channel of the module	No
— internal comparison point	Yes; with BaseUnit type A1
— Reference channel of the group	Yes
— Number of reference channel groups	4; Group 0 to 3
— fixed reference temperature	Yes
Cable length	
• shielded, max.	200 m; 100 m for thermocouples
Analog value generation for the inputs	
Measurement principle	integrating (Sigma-Delta)
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Basic conversion time, including integration time (ms)	

— additional processing time for wire-break check	1 ms
• Interference voltage suppression for interference frequency f1 in Hz	16.6 / 50 / 60 Hz / off
• Conversion time (per channel)	180/60/50/1.25 ms
Smoothing of measured values	
• Number of smoothing levels	4; None; 4/8/16 times
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
Encoder	
Connection of signal encoders	
• for voltage measurement	Yes
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	-70 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.03 %
Operational error limit in overall temperature range	
• Voltage, relative to input range, (+/-)	0.1 %; 0.3 % when SFU OFF
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to input range, (+/-)	0.05 %; 0.2 % when SFU OFF
Interference voltage suppression for $f = n \times (f1 \pm 1 \%)$, f1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	70 dB
• Common mode voltage, max.	60 V; DC
• Common mode interference, min.	90 dB
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	Yes; two upper and two lower limit values in each case
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire break	Yes; channel by channel
• Group error	Yes
• Overflow/Underflow	Yes; channel by channel
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; green/red LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	Yes
Permissible potential difference	
between the inputs (UCM)	60 V DC
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for applications according to AMS 2750	Yes; Declaration of Conformity, see online support entry 109757262
Suitable for applications according to CQI-9	Yes; Based on AMS 2750 E
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	

— global warming potential, (total) [CO2 eq]	9.32 kg
— global warming potential, (during production) [CO2 eq]	4.97 kg
— global warming potential, (during operation) [CO2 eq]	4.79 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.449 kg

Ambient conditions

Ambient temperature during operation	
• horizontal installation, min.	-30 °C; < 0 °C as of FS02
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C; < 0 °C as of FS02
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Absolute humidity	
• dew point, min.	-60 °C; suitable for dry room applications

Dimensions

Width	15 mm
Height	73 mm
Depth	58 mm

Weights

Weight, approx.	33 g
-----------------	------

Classifications

	Version	Classification
eClass	14	27-24-26-01
eClass	12	27-24-26-01
eClass	9.1	27-24-26-01
eClass	9	27-24-26-01
eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	10	EC001596
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval



[China RoHS](#)



last modified:

2/1/2026