

MEF EMC-FILTER 1-PHASE 2-STAGE

I:2A U:250 VAC/300 VDC snap on

Art.No.: 10461



Weight: 0.322 kg

Country of origin: IT

Model designation: MEF 1/2 SY 2A T

Current: 2 A

DIN-rail mountable

Attenuation curves on request.
against symmetrical interferences[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MEF 1/2 SY 2A T

Commercial data

URL Webshop	https://shop.murrelektronik.com/10461
GTIN	4048879029377
Suitable for application range	Power Supply Units, Devices with high repetition rates of switching operations, Phase angle control, supply of universal motors, after transformers
Suitable for type of fault	symmetrical interferences
ECLASS-6.0	27130806
ECLASS-6.1	27420201
ECLASS-7.0	27420290
ECLASS-7.1	27420290
ECLASS-8.0	27420290
ECLASS-8.1	27420290
ECLASS-9.0	27420208
ECLASS-9.1	27420290
ECLASS-10.0.1	27420290
ECLASS-10.1	27420208
ECLASS-11.0	27420290
ECLASS-11.1	27420208
ECLASS-12.0	27420208
ECLASS-13.0	27420290
ECLASS-14.0	27420290
ETIM-5.0	EC002498
ETIM-6.0	EC002498
ETIM-7.0	EC002498
ETIM-8.0	EC002498
customs tariff number	85363010
EAN	4048879029377
Packaging unit	1

Electrical data

Leakage current max.	5 mA @ 250 V AC, 50 Hz
----------------------	------------------------

Electrical data | Supply

Power frequency	50 ... 60 Hz
Operating voltage AC max.	250 V
Operating voltage DC max.	300 V

Electrical data | Output

Overload current	18× (IN t) max. 0.5 ms; 1.5× (IN t) max. 1 min. (1× per hour)
------------------	---

Installation

Connection cross-section solid min.	0,2 mm ²
Connection cross-section solid max.	6 mm ²
Connection cross-section stranded/fine-stranded min.	0,2 mm ²
Connection cross-section stranded/fine-stranded max.	4 mm ²
AWG number solid min.	24
AWG number solid max.	9
AWG number stranded/fine stranded min.	24
AWG number stranded/fine stranded max.	11

Device protection | Electrical

Insulation test voltage L-N	2,7 kV
Insulation test voltage L-L	2,1 kV
Duration insulation test voltage	2 s

Mechanical data | Mounting data

Height	107 mm
--------	--------

Width	56 mm
Depth	39 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Climatic category (EN IEC 60068-1)	25/085/21
------------------------------------	-----------

Connection type 3

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green-yellow
Connection	Screw terminals SK
PIN 1	PE
Family construction form	terminal
No. of poles	2
Color contact carrier	gray
Connection	Screw terminals SK
PIN 1	L
PIN 2	N
Family construction form	terminal
No. of poles	2
Color contact carrier	gray
Connection	Screw terminals SK
PIN 1	L'
PIN 2	N'