

MEF EMC-FILTER 3-PHASE 1-STAGE WITH NEUTRAL

I:10A U:4x500 VAC

Art.No.: 10571

Weight: 1.000 kg

Country of origin: IT

Model designation: MEF 3/1 N HD 10A T

Current: 10 A

with neutral



with increased damping

Attenuation curves on request.

The 3-phase and one-stage EMC filters MEF 3/1 are used in the range 0.1...30 MHz and dampen interferences found in cables from the mains, supply units and control systems. They are suitable for TN-S, TN-C-S, and TT networks. The best results are obtained with short connection cables (suggestion: earth connection < 10 cm) of the largest possible cross-section. The EMC filters are bi-directional. They reduce symmetrical and asymmetrical interferences that regularly appear with electronically controlled three phase units through mains influences.

[Link to Product](#)

Illustration



Product may differ from Image



Header	
Material short text	MEF 3/1 N HD 10A T
Commercial data	
URL Webshop	https://shop.murrelektronik.com/10571
GTIN	4048879029100
ECLASS-6.0	27130806
ECLASS-6.1	27420201
ECLASS-7.0	27420290
ECLASS-7.1	27420290
ECLASS-8.0	27420290
ECLASS-8.1	27420290
ECLASS-9.0	27420208
ECLASS-9.1	27420290
ECLASS-10.0.1	27420290
ECLASS-10.1	27420208
ECLASS-11.0	27420290
ECLASS-11.1	27420208
ECLASS-12.0	27420208
ECLASS-13.0	27420290
ECLASS-14.0	27420290
ETIM-5.0	EC002498
ETIM-6.0	EC002498
ETIM-7.0	EC002498
ETIM-8.0	EC002498
customs tariff number	85363010
EAN	4048879029100
Packaging unit	1
Electrical data	
Leakage current max.	15 mA @ 250 V AC, 50 Hz
Electrical data Supply	
Power frequency	50 ... 60 Hz
Operating voltage AC max.	500 V
Electrical data Input	
Phase number input	3
Electrical data Output	
Overload current	18× (IN t) max. 0.5 ms; 1.5× (IN t) max. 1 min. (1× per hour)
Installation	
Connection cross-section solid min.	0,2 mm ²
Connection cross-section solid max.	10 mm ²
Connection cross-section stranded/fine-stranded min.	0,2 mm ²
Connection cross-section stranded/fine-stranded max.	6 mm ²
AWG number solid min.	24
AWG number solid max.	7
AWG number stranded/fine stranded min.	24
AWG number stranded/fine stranded max.	9
Installation Connection	
Mounting set	M6
Device protection Electrical	
Insulation test voltage L-N	3,3 kV

Insulation test voltage L-L	3,1 kV
-----------------------------	--------

Duration insulation test voltage	2 s
----------------------------------	-----

Mechanical data | Mounting data

Height	153 mm
--------	--------

Width	130 mm
-------	--------

Depth	100 mm
-------	--------

Mounting method	screwed
-----------------	---------

Environmental characteristics | Climatic

Climatic category (EN IEC 60068-1)	25/085/21
------------------------------------	-----------

Connection type 2

Family construction form	terminal
--------------------------	----------

No. of poles	4
--------------	---

Gender	female
--------	--------

Color contact carrier	gray
-----------------------	------

Connection	Screw terminals SK
------------	--------------------

PIN 1	L 1
-------	-----

PIN 2	L 2
-------	-----

PIN 3	L 3
-------	-----

PIN 4	N
-------	---

Family construction form	terminal
--------------------------	----------

No. of poles	4
--------------	---

Gender	female
--------	--------

Color contact carrier	gray
-----------------------	------

Connection	Screw terminals SK
------------	--------------------

PIN 1	L 1'
-------	------

PIN 2	L 2'
-------	------

PIN 3	L 3'
-------	------

PIN 4	N'
-------	----