



SIMATIC DP, POWER M. F-PM-E PPM PROFIsafe, for ET 200SP; 24 V DC safe shutdown of DQ and F-DQ up to PL D/SIL2 or PL E/SIL3 2 for safe dig. inputs 1 for safe dig. output PPM

General information	
Product type designation	F-PM-E 24 V DC/8 A PPM ST
usable BaseUnits	BU type C0
Color code for module-specific color-coded label	CC52
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V12
• STEP 7 configurable/integrated from version	V5.5 SP3 / -
• PROFINET from GSD version/GSD revision	V2.31
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	75 mA; without load
Current consumption, max.	21 mA; From the backplane bus
Output voltage	
Rated value (DC)	24 V
Encoder supply	
Number of outputs	2
Short-circuit protection	Yes; Electronic (response threshold 0.7 A to 2.1 A)
Output current	
• up to 60 °C, max.	0.3 A
24 V encoder supply	
• 24 V	Yes; min. L+ (-1.5 V)
• Short-circuit protection	Yes
• Output current, max.	600 mA; Total current of all encoders
Power	
Power consumption from the backplane bus	70 mW
Power loss	
Power loss, typ.	5 W
Address area	
Address space per module	
• Inputs	7 byte
• Outputs	5 byte
Hardware configuration	
Automatic encoding	Yes

• Electronic coding element type F	Yes
Digital inputs	
Number of digital inputs	2
Sourcing/sinking input	Yes; P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input voltage	
• Type of input voltage	DC
• Rated value (DC)	24 V
• for signal "0"	-30 to +5 V
• for signal "1"	+15 to +30 V
Input current	
• for signal "1", typ.	3.7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes
— at "0" to "1", min.	0.4 ms
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.4 ms
— at "1" to "0", max.	20 ms
for technological functions	
— Parameterizable	No
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	500 m
Digital outputs	
Number of digital outputs	1
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes
• Response threshold, typ.	> 14.8 A
Open-circuit detection	Yes
• Response threshold, typ.	8 mA
Overload protection	Yes
• Response threshold, typ.	8.8 A
Limitation of inductive shutdown voltage to	Max. -1.5 V
Switching capacity of the outputs	
• with resistive load, max.	8 A
• on lamp load, max.	100 W
Load resistance range	
• lower limit	3 Ω
• upper limit	2 000 Ω
Output voltage	
• for signal "1", min.	24 V; L+ (-0.5 V)
Output current	
• for signal "1" rated value	8 A
• for signal "0" residual current, max.	1.5 mA; PP-switching: max. 1.5 mA; PM-switching: max. 1 mA
Switching frequency	
• with resistive load, max.	10 Hz; Symmetrical
• with inductive load, max.	0.1 Hz; according to IEC 60947-5-1, DC-13, symmetrical
• on lamp load, max.	4 Hz; Symmetrical
Total current of the outputs	
• Current per channel, max.	8 A; note derating data in the manual
• Current per module, max.	8 A; note derating data in the manual
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	500 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes; See Chapter "Alarms/diagnostic messages" in the manual
Substitute values connectable	No
Alarms	

• Diagnostic alarm • Hardware interrupt	Yes No		
Diagnostics indication LED			
• RUN LED • ERROR LED • Monitoring of the supply voltage (PWR-LED) • Channel status display • for channel diagnostics • for module diagnostics	Yes; green LED Yes; red LED Yes; green PWR LED Yes; green LED Yes; red LED Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels • between the channels and backplane bus • between the channels and the power supply of the electronics	No Yes No		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Suitable for safety functions	Yes		
Ecological footprint			
• environmental product declaration	Yes		
Global warming potential			
— global warming potential, (total) [CO2 eq] — global warming potential, (during production) [CO2 eq] — global warming potential, (during operation) [CO2 eq] — global warming potential, (after end of life cycle) [CO2 eq]	88.3 kg 13.1 kg 76.6 kg -1.37 kg		
Highest safety class achievable in safety mode			
• Performance level according to ISO 13849-1 • SIL acc. to IEC 61508	PLe SIL 3		
Probability of failure (for service life of 20 years and repair time of 100 hours)			
— Low demand mode: PFDavg in accordance with SIL2 — Low demand mode: PFDavg in accordance with SIL3 — High demand/continuous mode: PFH in accordance with SIL2 — High demand/continuous mode: PFH in accordance with SIL3	< 2.00E-04 < 2.00E-05 < 1.00E-08 1/h < 1.00E-09 1/h		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max.	0 °C 60 °C 0 °C 50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	4 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP System Manual		
Dimensions			
Width	20 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	70 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-11
	eClass	14	27-24-26-11

eClass	12	27-24-26-11
eClass	9.1	27-24-26-11
eClass	9	27-24-26-11
eClass	8	27-24-26-11
eClass	7.1	27-24-26-11
eClass	6	27-24-26-11
ETIM	10	EC002583
ETIM	9	EC002583
ETIM	8	EC002583
ETIM	7	EC002583
IDEA	4	3575
UNSPSC	15	32-15-17-06

Approvals / Certificates

General Product Approval




General Product Approval

For use in hazardous locations



For use in hazardous locations

Functional Safety



Functional Safety

Maritime application



Maritime application

Environment

Industrial Communication



last modified:

10/23/2025