



SIMATIC ET 200SP, TM count 1x 24 V Counter module, 1 channel for 24 V incremental encoder or pulse encoder, 3 DI, 2 DQ Suitable for BU type A0, packing quantity: 1 unit,

General information	
Product type designation	TM Count 1x24V
Firmware version	V2.0
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color-coded label	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V15 SP1 or higher
• STEP 7 configurable/integrated from version	V5.6 and higher
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.34
Supply voltage	
Rated value (DC)	24 V
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	19.2 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes
Input current	
Current consumption, max.	60 mA; without load
Encoder supply	
Number of outputs	1
24 V encoder supply	
• 24 V	Yes; L+ (-0.8 V)
• Short-circuit protection	Yes; electronic/thermal
• Output current, max.	300 mA
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Inputs	16 byte; 4 bytes in Fast mode
• Outputs	12 byte; 4 bytes for Motion Control, 0 bytes for Fast mode
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type B

Digital inputs	
Number of digital inputs	3
Digital inputs, parameterizable	Yes
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Digital input functions, parameterizable	
• Gate start/stop	Yes
• Capture	Yes
• Synchronization	Yes
• Freely usable digital input	Yes
• Probe	Yes
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-5 ... +5 V
• for signal "1"	+11 to +30V
• permissible voltage at input, min.	-30 V; -5 V continuous, -30 V brief reverse polarity protection
• permissible voltage at input, max.	30 V
Input current	
• for signal "1", typ.	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; none / 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms
for technological functions	
— parameterizable	Yes
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Digital outputs	
Type of digital output	Transistor
Number of digital outputs	2
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes; electronic/thermal
• Response threshold, typ.	1 A
Limitation of inductive shutdown voltage to	L+ (-53 V)
Controlling a digital input	Yes
Digital output functions, parameterizable	
• Switching tripped by comparison values	Yes
• Freely usable digital output	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A; Per digital output
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	12 kΩ
Output voltage	
• for signal "1", min.	23.2 V; L+ (-0.8 V)
Output current	
• for signal "1" rated value	0.5 A; Per digital output
• for signal "1" permissible range, max.	0.6 A; Per digital output
• for signal "1" minimum load current	2 mA
• for signal "0" residual current, max.	0.5 mA
Output delay with resistive load	
• "0" to "1", max.	50 μs
• "1" to "0", max.	50 μs
Switching frequency	
• with resistive load, max.	10 kHz
• with inductive load, max.	0.5 Hz; Acc. to IEC 60947-5-1, DC-13; observe derating curve
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per module, max.	1 A

Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
Encoder signals, incremental encoder (asymmetrical)	
• Input voltage	24 V
• Input frequency, max.	200 kHz
• Counting frequency, max.	800 kHz; with quadruple evaluation
• Cable length, shielded, max.	600 m; depending on input frequency, encoder and cable quality; max. 50 m at 200 kHz
• Signal filter, parameterizable	Yes
• Incremental encoder with A/B tracks, 90° phase offset	Yes
• Incremental encoder with A/B tracks, 90° phase offset and zero track	Yes
• pulse encoder	Yes
• pulse encoder with direction	Yes
• pulse encoder with one impulse signal per count direction	Yes
Interface types	
• Sourcing/sinking input	Yes
• Input characteristic curve in accordance with IEC 61131, type 3	Yes
Interfaces	
Number of RS 485 interfaces	0
Interrupts/diagnostics/status information	
Substitute values connectable	Yes; Parameterizable
Alarms	
• Diagnostic alarm	Yes
• Hardware interrupt	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire break	Yes
• Short-circuit	Yes
• A/B transition error at incremental encoder	Yes
• Group error	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for module diagnostics	Yes; green/red DIAG LED
• Status indicator forward counting (green)	Yes
• Status indicator backward counting (green)	Yes
Integrated Functions	
Counter	Yes
• Number of counters	1
• Counting frequency, max.	800 kHz; with quadruple evaluation
Fast mode	Yes
Counting functions	
• Can be used with TO High_Speed_Counter	Yes
• Continuous counting	Yes
• Counter response parameterizable	Yes
• Hardware gate via digital input	Yes
• Software gate	Yes
• Event-controlled stop	Yes
• Synchronization via digital input	Yes
• Counting range, parameterizable	Yes
Comparator	
— Number of comparators	2
— Direction dependency	Yes

— Can be changed from user program	Yes		
Position detection			
• Incremental acquisition	Yes		
• Suitable for S7-1500 Motion Control	Yes		
Measuring functions			
• Measuring time, parameterizable	Yes		
• Dynamic measurement period adjustment	Yes		
• Number of thresholds, parameterizable	2		
Measuring range			
— Frequency measurement, min.	0.04 Hz		
— Frequency measurement, max.	800 kHz		
— Cycle duration measurement, min.	1.25 µs		
— Cycle duration measurement, max.	25 s		
Accuracy			
— Frequency measurement	100 ppm; depending on measuring interval and signal evaluation		
— Cycle duration measurement	100 ppm; depending on measuring interval and signal evaluation		
— Velocity measurement	100 ppm; depending on measuring interval and signal evaluation		
Potential separation			
Potential separation channels			
• between the channels and backplane bus	Yes		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Suitable for safety functions	No		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C		
• horizontal installation, max.	60 °C; Observe derating		
• vertical installation, min.	-30 °C		
• vertical installation, max.	50 °C; Observe derating		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Absolute humidity			
• dew point, min.	-60 °C; suitable for dry room applications		
Decentralized operation			
to SIMATIC S7-300	Yes		
to SIMATIC S7-400	Yes		
to SIMATIC S7-1200	Yes		
to SIMATIC S7-1500	Yes		
to standard PROFIBUS master	Yes		
to standard PROFINET controller	Yes		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	45 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-05
	eClass	14	27-24-26-05
	eClass	12	27-24-26-05
	eClass	9.1	27-24-26-05
	eClass	9	27-24-26-05
	eClass	8	27-24-26-05
	eClass	7.1	27-24-26-05
	eClass	6	27-24-26-05

ETIM	10	EC001601
ETIM	9	EC001601
ETIM	8	EC001601
ETIM	7	EC001601
IDEA	4	3567
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval

For use in hazardous locations



[China RoHS](#)



[EM](#)

For use in hazardous locations

[CCC-Ex](#)



[Type Examination Certificate](#)



[Miscellaneous](#)

[CCC-Ex](#)

Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

last modified:

5/12/2026