

MIRO 6.2 PLUGGABLE COMPL.MODULE OUTPUT RELAY

IN: 125 VAC/DC - OUT: 250 VAC/30VDC / 6 A

Art.No.: 3000-16013-3100025

Weight: 0.032 kg

Country of origin: CN



Model designation: Miro 6,2-Ausgrel.Komplettmodul 115VAC/DC

1 NO/NC contact

6 A

115 V AC/DC

Spring clamp terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

Miro 6,2-Ausgrel.Komplettmodul 115VAC/DC

Commercial data

URL Webshop	https://shop.murrelektronik.com/3000-16013-3100025
GTIN	4048879021425
ECLASS-6.0	27371601
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879021425
Packaging unit	1

Electrical data | Input

Input voltage AC min.	88 V
Input voltage AC max.	138 V
Input voltage DC min.	88 V
Input voltage DC max.	138 V
Input current	8 mA
Control voltage AC min.	115 V
Control voltage AC max.	125 V
Control voltage DC min.	115 V
Control voltage DC max.	125 V

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	30 V
Switching current max.	6 A
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1.500 VA
Power rating DC max.	180 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 1.5 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.2 A @ 110 V 0.1 A @ 230 V

Diagnostics

Status indication LED	green
-----------------------	-------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Electrical lifetime NC	10.000 cycles

Electrical lifetime NO	30.000 cycles
------------------------	---------------

Rated insulation voltage	250 V
--------------------------	-------

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data

Response time max.	8 ms
--------------------	------

Drop-out time max.	4 ms
--------------------	------

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Height	93 mm
--------	-------

Width	6,2 mm
-------	--------

Depth	75,6 mm
-------	---------

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	(EN 60715), mounting rail
----------------------------	---------------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Connection type 5

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	12
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	11
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	14
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	A 1
-------	-----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	A 2
-------	-----