

Siemens
EcoTech



Figure similar

SIMATIC DP, Electronic modules for ET 200 PRO 4 AO U High Feature, ± 10 V; 0...10V; 1...5V, Channel diagnostics; incl. bus module, Connection module IO 6ES7194-4..00-0AA0 order separately

Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes; against destruction
Input current	
from supply voltage 1L+, max.	65 mA
from backplane bus 3.3 V DC, max.	10 mA
Actuator supply	
Number of outputs	4
Short-circuit protection	Yes; per module
Output current	
• up to 55 °C, max.	1 A
Power loss	
Power loss, typ.	1.7 W
Address area	
Address space per module	
• Address space per module, max.	8 byte
Analog outputs	
Number of analog outputs	4
Voltage output, short-circuit protection	Yes; per channel, electronic to chassis
Voltage output, short-circuit current, max.	50 mA
Cycle time (all channels) max.	3 ms
Output ranges, voltage	
• 0 to 10 V	Yes
• 1 V to 5 V	Yes
• -10 V to +10 V	Yes
Connection of actuators	
• for voltage output two-wire connection	Yes
• for voltage output four-wire connection	Yes
Load impedance (in rated range of output)	
• with voltage outputs, min.	1 000 Ω
• with voltage outputs, capacitive load, max.	1 μ F
Destruction limits against externally applied voltages and currents	
• Voltages at the outputs towards MANA	16 V; Permanent
Cable length	
• shielded, max.	30 m

Analog value generation for the outputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	15 bit; at -10 to +10 V; 14 bit at 1 to 5 V; 15 bit at 0 to 10 V
• Conversion time (per channel)	0.7 ms
Settling time	
• for resistive load	0.1 ms
• for capacitive load	6 ms
Errors/accuracies	
Output ripple (relative to output range, bandwidth 0 to 50 kHz), (+/-)	0.02 %
Linearity error (relative to output range), (+/-)	0.1 %
Temperature error (relative to output range), (+/-)	0.01 %/K
Repeat accuracy in steady state at 25 °C (relative to output range), (+/-)	0.05 %
Operational error limit in overall temperature range	
• Voltage, relative to output range, (+/-)	0.2 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to output range, (+/-)	0.15 %
Interrupts/diagnostics/status information	
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes; Parameterizable
• Hardware interrupt	No
Diagnoses	
• Diagnostic information readable	Yes
• Wire break	No
• short-circuit	Yes; per channel, not in zero range
Diagnostics indication LED	
• Group error SF (red)	Yes
Potential separation	
Potential separation analog outputs	
• between the channels	No
• between the channels and backplane bus	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Dimensions	
Width	45 mm
Height	130 mm
Depth	35 mm
Weights	
Weight, approx.	150 g
Classifications	


	Version	Classification
eClass	16	27-24-26-01
eClass	14	27-24-26-01
eClass	12	27-24-26-01
eClass	9.1	27-24-26-01
eClass	9	27-24-26-01
eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	10	EC001596
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval




General Product Approval	Test Certificates	Maritime application
--------------------------	-------------------	----------------------



Maritime application	other
----------------------	-------



other	Railway	Environment
-------	---------	-------------



last modified: 10/23/2025