

MIRO 6.2 pluggable Plug-in module Optocoupler

IN: 24 VDC - OUT: 24 VDC / 6 A

Art.No.: 3000-32522-2100040

Weight: 0.004 kg

Country of origin: CZ


Model designation: Optocoupler 24V/24V 6A (plug-in module)

Transistor 6 A


24 V DC

Link to Product

Illustration



Product may differ from Image



Header

Material short text	Optocoupler 24V/24V 6A (plug-in module)
---------------------	---

Commercial data

URL Webshop	https://shop.murrelektronik.com/3000-32522-2100040
GTIN	4048879535175
ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-7.1	27371604
ECLASS-8.0	27371604
ECLASS-8.1	27371604
ECLASS-9.0	27371604
ECLASS-9.1	27371604
ECLASS-10.0.1	27371604
ECLASS-10.1	27371604
ECLASS-11.0	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604
ECLASS-14.0	27371604

The information in this Product-PDF has been compiled with the utmost care.

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-01-29

ETIM-5.0	EC001504
ETIM-6.0	EC001504
ETIM-7.0	EC001504
ETIM-8.0	EC001504
customs tariff number	85414900
EAN	4048879535175
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	18 V
Input voltage DC max.	30 V
Input current	9 mA

Electrical data | Output

Forward voltage max.	240 mV
Switch on delay max.	15 µs
Switch off delay max.	31 µs
Voltage switching DC min.	3 V
Switching voltage DC max.	30 V
Switching current min.	10 mA
Switching current max.	6 A
Switching frequency ohmic max.	500 Hz
Switching frequency inductive max.	50 Hz

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Rated surge voltage	2.5 kV
Rated insulation voltage	50 V

Mechanical data | Mounting data

Height	15 mm
Width	5 mm
Depth	28 mm
Mounting method	inserted

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	50 °C