

**VALVE PLUG SUPPRESSOR FORM A - 18MM**

RC and LED, 48VAC/DC/30VA/W

Art.No.: 3124071

Weight: 0.036 kg



Country of origin: CZ

Model designation: VBS-LEDY+RC 22/48 U

48 V AC/DC

RC + LED

Remove plug gasket when fitting adapter. Other LED colors on request.

**[Link to Product](#)****Illustration**

Product may differ from Image

**Header**

Material short text

VBS-LEDY+RC 22/48 U

**Commercial data**

URL Webshop

<https://shop.murrelektronik.com/3124071>

|                                                 |                 |
|-------------------------------------------------|-----------------|
| GTIN                                            | 4048879012126   |
| ECLASS-6.0                                      | 27371013        |
| ECLASS-6.1                                      | 27371013        |
| ECLASS-7.0                                      | 27371013        |
| ECLASS-7.1                                      | 27371013        |
| ECLASS-8.0                                      | 27371013        |
| ECLASS-8.1                                      | 27371013        |
| ECLASS-9.0                                      | 27371013        |
| ECLASS-9.1                                      | 27371013        |
| ECLASS-10.0.1                                   | 27371013        |
| ECLASS-10.1                                     | 27371013        |
| ECLASS-11.0                                     | 27371013        |
| ECLASS-11.1                                     | 27371013        |
| ECLASS-12.0                                     | 27371013        |
| ECLASS-13.0                                     | 27371013        |
| ECLASS-14.0                                     | 27371013        |
| ETIM-5.0                                        | EC000683        |
| ETIM-6.0                                        | EC000683        |
| ETIM-7.0                                        | EC000683        |
| ETIM-8.0                                        | EC000683        |
| customs tariff number                           | 85363010        |
| EAN                                             | 4048879012126   |
| Packaging unit                                  | 1               |
| <b>Electrical data</b>                          |                 |
| Drop-out delay time max.                        | 20 ms           |
| Holding power max.                              | 30 W            |
| <b>Electrical data   Supply</b>                 |                 |
| Cut-off peak voltage max.                       | 90 V            |
| <b>Electrical data   Input</b>                  |                 |
| Input voltage AC min.                           | 24 V            |
| Input voltage AC max.                           | 53 V            |
| Input voltage DC min.                           | 24 V            |
| Input voltage DC max.                           | 53 V            |
| <b>Diagnostics</b>                              |                 |
| Status indication LED                           | yellow          |
| <b>Device protection   Media</b>                |                 |
| Flame resistance                                | flame retardant |
| <b>Mechanical data   Material data</b>          |                 |
| Material housing                                | PA              |
| Color housing                                   | black           |
| Material contact                                | Bronze          |
| Coating contact                                 | silver-plated   |
| <b>Mechanical data   Mounting data</b>          |                 |
| Height                                          | 37 mm           |
| Width                                           | 53 mm           |
| Depth                                           | 33 mm           |
| <b>Environmental characteristics   Climatic</b> |                 |
| Operating temperature min.                      | -20 °C          |
| Operating temperature max.                      | 60 °C           |
| Housing temperature max. (EN 61347-2-13)        | 130 °C          |