

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | [shop@murrinc.com](mailto:shop@murrinc.com) | [shop.murrinc.com](http://shop.murrinc.com)

|                       |               |
|-----------------------|---------------|
| ETIM-5.0              | EC000020      |
| ETIM-6.0              | EC000020      |
| ETIM-7.0              | EC000020      |
| ETIM-8.0              | EC000020      |
| customs tariff number | 85366990      |
| EAN                   | 4048879601061 |
| Packaging unit        | 1             |

**Device protection | Electrical**

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP20 |
|-------------------------------------|------|

**Mechanical data | Mounting data**

|        |         |
|--------|---------|
| Height | 87,5 mm |
| Width  | 50,7 mm |
| Depth  | 43 mm   |

**Environmental characteristics | Climatic**

|                                          |                  |
|------------------------------------------|------------------|
| Operating temperature min.               | -5 °C            |
| Operating temperature max.               | 50 °C            |
| Ambient temperature (storage, transport) | -10 °C ... 60 °C |

**Shielding plate**

|                             |                  |
|-----------------------------|------------------|
| Connection information      | Threaded hole M4 |
| Tightening torque           | 0,9 Nm           |
| Tightening torque tolerance | ± 0,1 Nm         |

**Swiss**

|                               |                           |
|-------------------------------|---------------------------|
| Connection                    | Spring clamp terminals FK |
| No. of poles                  | PE                        |
| Connections per pole          | 2                         |
| Protection contact present    | Yes                       |
| Connection cross section max. | 1,5 mm <sup>2</sup>       |
| AWG number max.               | 16                        |
| Operating voltage AC          | 250 V                     |
| Operating current             | 10 A                      |