

MODLINK MSDD SINGLE COMBI INSERT BRAZIL

1x SUB-D9 ST/BU
Art.No.: 4000-68000-4610004
Weight: 0.052 kg
Country of origin: DE
Model designation: Fr.Modul-N-250-10-SC+DB9M/F

1x Brazil
1x SUB-D9 (male/female)
1x SUB-D9 cut-out

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Fr.Modul-N-250-10-SC+DB9M/F
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-4610004
GTIN	4048879601160
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879601160
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	87,5 mm
Width	50,7 mm
Depth	30,7 mm

Environmental characteristics | Climatic

Operating temperature min.	5 °C
Operating temperature max.	35 °C
Ambient temperature (storage, transport)	5 °C ... 35 °C

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Tightening torque tolerance	± 0,1 Nm

SUB-D9

Family construction form	SUB-D9
Gender	male
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	female
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA