


EOL - Modlink MSDD-set: Frame 4000-68113-0000000,

discontinued - End of Life Date: 2024-12-31

Art.No.: 4000-68113-1110000  
Weight: 0.330 kg  
Country of origin: DE  
Model designation: X MSDD\_1MV\_9B/B,S/S+RJ45\_

Link to Product

Illustration



Product may differ from Image



| Commercial data |          |
|-----------------|----------|
| ECLASS-6.0      | 27189217 |
| ECLASS-6.1      | 27189217 |
| ECLASS-7.0      | 27189217 |
| ECLASS-8.0      | 27189217 |
| ECLASS-9.0      | 27182806 |
| ECLASS-10.1     | 27182806 |

|                       |               |
|-----------------------|---------------|
| ECLASS-11.1           | 27182806      |
| ECLASS-12.0           | 27182806      |
| ETIM-5.0              | EC002625      |
| ETIM-6.0              | EC002625      |
| ETIM-7.0              | EC002625      |
| ETIM-8.0              | EC002625      |
| customs tariff number | 85366990      |
| customs tariff number | 85366990      |
| customs tariff number | 85366990      |
| customs tariff number | 85366990      |
| EAN                   | 4048879036122 |
| EAN                   | 4048879036122 |
| EAN                   | 4048879036122 |
| EAN                   | 4048879036122 |
| Packaging unit        | 1             |
| Packaging unit        | 1             |
| Packaging unit        | 1             |
| Packaging unit        | 1             |

**Frame**

|                                               |                       |
|-----------------------------------------------|-----------------------|
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |
| Operating temperature max.                    | 60 °C                 |
| Storage temperature min.                      | -25 °C                |
| Storage temperature max.                      | 60 °C                 |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Material housing                              | Fine zinc die casting |
| Coating housing                               | surface finished      |

**SUB-D9**

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Operating current                     | 3 A                                            |
| Current operating max. (UL)           | 175 mA                                         |
| Family construction form              | SUB-D9                                         |
| Family type Back side                 | SUB-D9                                         |
| Gender                                | male                                           |
| Gender Rear                           | male                                           |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 9                                              |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |