

**EOL - Modlink MSDD-set: Frame 4000-68122-0000000,**

discontinued - End of Life Date: 2024-12-31

Art.No.: 4000-68122-0011100

Weight: 0.781 kg

Country of origin: DE

Model designation: X MSDD\_2SW\_VDE MIT LED\_25B/S+RJ12,45\_

[Link to Product](#)**Illustration**



Product may differ from Image



| Commercial data                               |               |
|-----------------------------------------------|---------------|
| ECLASS-6.0                                    | 27189217      |
| ECLASS-6.1                                    | 27189217      |
| ECLASS-7.0                                    | 27189217      |
| ECLASS-8.0                                    | 27189217      |
| ECLASS-9.0                                    | 27182806      |
| ECLASS-10.1                                   | 27182806      |
| ECLASS-11.1                                   | 27182806      |
| ECLASS-12.0                                   | 27182806      |
| ETIM-5.0                                      | EC002625      |
| ETIM-6.0                                      | EC002625      |
| ETIM-7.0                                      | EC002625      |
| ETIM-8.0                                      | EC002625      |
| customs tariff number                         | 85366990      |
| customs tariff number                         | 85366990      |
| customs tariff number                         | 85366990      |
| customs tariff number                         | 85366990      |
| EAN                                           | 4048879035903 |
| EAN                                           | 4048879035903 |
| EAN                                           | 4048879035903 |
| EAN                                           | 4048879035903 |
| Packaging unit                                | 1             |
| Packaging unit                                | 1             |
| Packaging unit                                | 1             |
| Packaging unit                                | 1             |
| Frame                                         |               |
| Degree of protection (EN IEC 60529)           | IP65          |
| Operating temperature min.                    | -10 °C        |
| Operating temperature max.                    | 60 °C         |
| Storage temperature min.                      | -25 °C        |
| Storage temperature max.                      | 60 °C         |
| Suitable for installation wall thickness min. | 1 mm          |
| Suitable for installation wall thickness max. | 5 mm          |

|                  |                       |
|------------------|-----------------------|
| Material housing | Fine zinc die casting |
| Coating housing  | KTL                   |

#### Germany (VDE)

|                               |                    |
|-------------------------------|--------------------|
| Connection cross section max. | 6 mm <sup>2</sup>  |
| AWG number max.               | 10                 |
| Operating voltage AC          | 250 V              |
| Operating current             | 16 A               |
| Status indication LED         | yellow             |
| Connection                    | Screw terminals SK |
| No. of poles                  | 2 + PE             |
| Connections per pole          | 2                  |
| Protection contact present    | yes                |

#### SUB-D25

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42,4 V                                         |
| Operating current                     | 3 A                                            |
| Current operating max. (UL)           | 175 mA                                         |
| Family construction form              | SUB-D25                                        |
| Family type Back side                 | SUB-D25                                        |
| Gender                                | female                                         |
| Gender Rear                           | male                                           |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 25                                             |

#### RJ12

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max.             | 48 V              |
| Operating voltage DC max.             | 48 V              |
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Operating current max.                | 1 A               |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ12              |
| Family type Back side                 | RJ12              |
| Looking techniques                    | Snap-in connector |

#### RJ45

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |