

Modlink MSDD-set: Frame 4000-68123-0000000,

insert 4000-68000-0040000 + 4000-68000-1310000


Art.No.: 4000-68123-0041310

Weight: 0.671 kg

Country of origin: CZ

Model designation: MSDD_2MV_NEMA5-15SK_USB+RJ45_

[Link to Product](#)**Illustration**



Product may differ from Image

Header

Material short text MSDD_2MV_NEMA5-15SK_USB+RJ45_

Commercial data

URL Webshop <https://shop.murrelektronik.com/4000-68123-0041310>

GTIN 4048879034692

ECLASS-6.0 27189217

ECLASS-6.1 27189217

ECLASS-7.0 27189217

ECLASS-7.1 27189217

ECLASS-8.0 27189217

ECLASS-8.1 27189217

ECLASS-9.0 27182806

ECLASS-9.1 27189217

ECLASS-10.0.1 27182806

ECLASS-10.1 27182806

ECLASS-11.0 27182806

ECLASS-11.1 27182806

ECLASS-12.0 27182806

ECLASS-13.0 27182806

ECLASS-14.0 27182806

ETIM-5.0 EC002625

ETIM-6.0 EC002625

ETIM-7.0 EC002625

ETIM-8.0 EC002625

customs tariff number 85366990

EAN 4048879034692

Packaging unit 1

customs tariff number 85366990

EAN 4048879034692

Packaging unit 1

Frame

Material housing Fine zinc die casting

Coating housing surface finished

Suitable for installation wall thickness min. 1 mm

Suitable for installation wall thickness max. 5 mm

Degree of protection (EN IEC 60529) IP65

Operating temperature min. -10 °C

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-25 °C
--------------------------	--------

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque	0,9 Nm
-------------------	--------

Tightening torque tolerance	± 0,1 Nm
-----------------------------	----------

USA

Connection	Screw terminals SK
------------	--------------------

No. of poles	PE
--------------	----

Connections per pole	2
----------------------	---

Protection contact present	Yes
----------------------------	-----

Connection cross section max.	2,5 mm ²
-------------------------------	---------------------

AWG number max.	14
-----------------	----

Operating voltage AC	125 V
----------------------	-------

Operating current	15 A
-------------------	------

USB

USB specification	3.0
-------------------	-----

Looking techniques	Snap-in connector
--------------------	-------------------

Data transmission rate max.	5.000 Mbit/s
-----------------------------	--------------

Operating voltage AC	48 V
----------------------	------

Operating voltage DC	48 V
----------------------	------

Operating current	1,5 A
-------------------	-------

Operating voltage AC max. (UL-listed)	30 V
---------------------------------------	------

Operating voltage DC max. (UL-listed)	42,4 V
---------------------------------------	--------

RJ45

Family construction form	RJ45
--------------------------	------

Looking techniques	Snap-in connector
--------------------	-------------------

Cable category min.	Cat5e
---------------------	-------

Family type Back side	RJ45
-----------------------	------

Operating voltage AC max. (UL-listed)	30 V
---------------------------------------	------

Operating voltage DC max. (UL-listed)	42,4 V
---------------------------------------	--------

Current operating max. (UL)	175 mA
-----------------------------	--------