

SCALANCE XR326-2C PoE WG; managed IE Switch; 19" rack; 24 x 1GE electrical PoE ports 2 x 10GE electrical combo PoE ports; electrical o. optical; LED diagnostics; reset button; console port; PROFINET device; network management function; Redundancy Manager; No UL/FM approval; Power supply 240 V AC (85 – 264 V).



product type designation	
product brand name	SCALANCE
product type designation	XR326-2C PoE WG
Technical Product Detail Page	https://l.siemens.com/1P6GK5326-2QS00-3RR3
transfer rate	
transfer rate	10, 100, 1000 Mbit/s
transfer rate	2.5, 5, 10 Gbit/s
interfaces / for communication / integrated	
number of electrical connections	
- for network components or terminal equipment - for Power-over-Ethernet / for network components or terminal equipment	26; RJ45 26
number of 10/100/1000 Mbit/s RJ45 ports	
with PoE	24; PoE Ports according to IEEE802.3at (30 W)
number of 10/100/1000/10000 Mbit/s RJ45 ports / with PoE	2
number of combo ports / with RJ45 interface for optical plug-in transceiver	2; 1000 Mbit/s, 2500 Mbit/s, 5000 Mbit/s, 10000 Mbit/s RJ45 port incl. PoE function and 1000 Mbit/s, 10000 Mbit/s SFP port
interfaces / other	
number of electrical connections	
- for operator console - for power supply	1 2
type of electrical connection	
- for operator console - for power supply	RJ11 IEC plug C14 and terminal block for additional PoE power supply (max. 2 additional PSR9230 PoE possible, PoE power expandable to 570 W)
supply voltage, current consumption, power loss	
supplied active power / of PSE / with PoE	
total / maximum	210 W
type of voltage / 1 / of the supply voltage	AC
- supply voltage / 1 / rated value - supply voltage / 1 / voltage range - consumed current / 1 / maximum - product component / 1 / fusing at power supply input - fuse protection type / 1 / at input for supply voltage	240 V; 100 V ... 240 V AC 85 ... 264 4 A Yes F 4 A / 250 V
ambient conditions	
ambient temperature	
- during operation - during storage - during transport	0 ... 60 °C -40 ... +85 °C -40 ... +85 °C
relative humidity	

at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP30
design, dimensions and weights	
design	19-inch rack
number of modular height units / relating to 19-inch cabinet	1
width	482.6 mm
height	43.6 mm
depth	227.3 mm
net weight	4.7 kg
material / of the enclosure	metal
fastening method	
19-inch installation	Yes
35 mm DIN-rail mounting	No
wall mounting	No
S7-300 rail mounting	No
S7-1500 rail mounting	No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
CLI	Yes
web-based management	Yes
MIB support	Yes
TRAPs via email	Yes
configuration with STEP 7	Yes
RMON	Yes
port mirroring	Yes
multiport mirroring	No
CoS	Yes
PROFINET IO diagnosis	Yes
switch-managed	Yes
PROFINET conformity class	B
network load class / according to PROFINET	III
protocol / is supported	
Telnet	Yes
HTTP	Yes
HTTPS	Yes
TFTP	Yes
FTP	Yes
BOOTP	Yes
GMRP	No
DCP	Yes
LLDP	Yes
SNMP v1	Yes
SNMP v2	Yes
SNMP v3	Yes
IGMP (snooping/querier)	Yes
identification & maintenance function	
I&M0 - device-specific information	Yes
I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
port diagnostics	Yes
statistics Packet Size	Yes
statistics packet type	Yes
error statistics	Yes

• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	
product function	
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	No
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	No
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• STP/RSTP	Yes
• STP	Yes
• RSTP	Yes
• MSTP	No
• RSTP big network support	Yes
• LACP	No
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	No
product functions / security	
product function	
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
product functions / time	
product function	
• SICLOCK support	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes
• IEEE 1588 profile default	No

standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UKCA marking	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4
• for immunity to EMC	EN 61000-6-2
standards, specifications, approvals / other	
certificate of suitability	
• railway application in accordance with EN 50155	No
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	931.69 kg
• during manufacturing	109.06999 kg
• during operation	822.07 kg
• after end of life	0.55 kg
product functions / general	
MTBF	25 a
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAX-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)
Approvals / Certificates	
Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing	109.07 kg
• global warming potential [CO2 eq] / during operation	822.07 kg
• global warming potential [CO2 eq] / after end of life	0.55 kg
• global warming potential [CO2 eq] / total	931.69 kg
Environment	General Product Approval



[TUEV](#)

General Product Approval	Test Certificates	Industrial Communication
China RoHS	Type Test Certificates/Test Report	PROFINET

last modified:

5/9/2026