

Modlink MSDD-set: Frame 4000-68123-0000000,

insert 4000-68000-0140000 + 4000-68000-1200000


Art.No.: 4000-68123-0141200

Weight: 0.656 kg

Country of origin: CN

Model designation: MSDD_2MV_VDE-OG.LED_2XRJ45_

[Link to Product](#)**Illustration**



Product may differ from Image

Header	
Material short text	MSDD_2MV_VDE-OG.LED_2XRJ45_
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68123-0141200
GTIN	4048879034562
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879034562
Packaging unit	1
customs tariff number	85366990
EAN	4048879034562
Packaging unit	1
Frame	
Material housing	Fine zinc die casting
Coating housing	surface finished
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-25 °C
--------------------------	--------

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque	0,9 Nm
-------------------	--------

Tightening torque tolerance	± 0,1 Nm
-----------------------------	----------

Germany (VDE)

Connection	Spring clamp terminals FK
------------	---------------------------

No. of poles	PE
--------------	----

Connections per pole	2
----------------------	---

Protection contact present	Yes
----------------------------	-----

Connection cross section max.	2,5 mm ²
-------------------------------	---------------------

AWG number max.	14
-----------------	----

Operating voltage AC	250 V
----------------------	-------

Operating current min.	10 A
------------------------	------

Operating current max.	16 A
------------------------	------

RJ45

Family construction form	RJ45
--------------------------	------

Looking techniques	Snap-in connector
--------------------	-------------------

Cable category min.	Cat5e
---------------------	-------

Family type Back side	RJ45
-----------------------	------

Operating voltage AC max. (UL-listed)	30 V
---------------------------------------	------

Operating voltage DC max. (UL-listed)	42,4 V
---------------------------------------	--------

Current operating max. (UL)	175 mA
-----------------------------	--------