

**Modlink MSDD-set: Frame 4000-68523-0000001,**

insert 4000-68000-4120000

Art.No.: 4000-68523-4120001  
Weight: 0.541 kg  
Country of origin: US  
Model designation: MSDD\_2metallic\_GFCI 15A+2xRJ45+3A fuse\_  
with touch protection

**Link to Product**

**Illustration**



Product may differ from Image

**Header**

Material short text MSDD\_2metallic\_GFCI 15A+2xRJ45+3A fuse\_

**Commercial data**

|             |                                                    |
|-------------|----------------------------------------------------|
| URL Webshop | https://shop.murrelektronik.com/4000-68523-4120001 |
| GTIN        | 4048879477970                                      |
| ECLASS-6.0  | 27144001                                           |
| ECLASS-6.1  | 27189217                                           |
| ECLASS-7.0  | 27189217                                           |
| ECLASS-7.1  | 27189217                                           |
| ECLASS-8.0  | 27189217                                           |

|                       |               |
|-----------------------|---------------|
| ECLASS-8.1            | 27189217      |
| ECLASS-9.0            | 27182806      |
| ECLASS-9.1            | 27189217      |
| ECLASS-10.0.1         | 27182806      |
| ECLASS-10.1           | 27182806      |
| ECLASS-11.0           | 27182806      |
| ECLASS-11.1           | 27182806      |
| ECLASS-12.0           | 27182806      |
| ECLASS-13.0           | 27182806      |
| ECLASS-14.0           | 27182806      |
| ETIM-5.0              | EC002625      |
| ETIM-6.0              | EC002625      |
| ETIM-7.0              | EC002625      |
| ETIM-8.0              | EC002625      |
| customs tariff number | 85366990      |
| EAN                   | 4048879477970 |
| Packaging unit        | 1             |
| customs tariff number | 85366990      |
| EAN                   | 4048879477970 |
| Packaging unit        | 1             |

**Mechanical data | Mounting data**

|        |        |
|--------|--------|
| Height | 88 mm  |
| Width  | 116 mm |
| Depth  | 72 mm  |

**Frame**

|                                               |          |
|-----------------------------------------------|----------|
| Material housing                              | PA       |
| Color housing                                 | black    |
| Material lid                                  | ABS      |
| Color cover                                   | metallic |
| Suitable for installation wall thickness min. | 1 mm     |
| Suitable for installation wall thickness max. | 5 mm     |
| Degree of protection (EN IEC 60529)           | IP65     |
| Operating temperature min.                    | -30 °C   |
| Operating temperature max.                    | 70 °C    |
| Storage temperature min.                      | -30 °C   |

**Fuse**

|                      |       |
|----------------------|-------|
| Operating voltage AC | 250 V |
| Operating voltage DC | 32 V  |
| Nominal current      | 3 A   |

**USA**

|                               |                    |
|-------------------------------|--------------------|
| Connection                    | Screw terminals SK |
| No. of poles                  | PE                 |
| Connections per pole          | 2                  |
| Protection contact present    | Yes                |
| Connection cross section max. | 6 mm <sup>2</sup>  |
| AWG number max.               | 10                 |
| Operating voltage AC          | 125 V              |
| Operating current             | 15 A               |

**RJ45**

|                          |                   |
|--------------------------|-------------------|
| Family construction form | RJ45              |
| Looking techniques       | Snap-in connector |
| Cable category min.      | Cat5e             |

|                                       |        |
|---------------------------------------|--------|
| Family type Back side                 | RJ45   |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Current operating max. (UL)           | 175 mA |