

Modlight70 Pro connecting modul 8 pole M12

side, Input 24VDC

Art.No.: 4000-76070-1400002  
Weight: 0.210 kg  
Country of origin: CZ  
Model designation: Modlight70 Pro BASE M12-8S


Basic  
Outlet on the side  
with M12 connection  
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



| Header              |                                                    |
|---------------------|----------------------------------------------------|
| Material short text | Modlight70 Pro BASE M12-8S                         |
| Commercial data     |                                                    |
| URL Webshop         | https://shop.murrelektronik.com/4000-76070-1400002 |
| GTIN                | 4048879758895                                      |
| ECLASS-6.0          | 27371232                                           |
| ECLASS-6.1          | 27371232                                           |
| ECLASS-7.0          | 27371232                                           |
| ECLASS-7.1          | 27371232                                           |
| ECLASS-8.0          | 27371232                                           |
| ECLASS-8.1          | 27371232                                           |
| ECLASS-9.0          | 27371232                                           |
| ECLASS-9.1          | 27371232                                           |
| ECLASS-10.0.1       | 27371232                                           |
| ECLASS-10.1         | 27371232                                           |
| ECLASS-11.0         | 27371232                                           |
| ECLASS-11.1         | 27371232                                           |
| ECLASS-12.0         | 27371232                                           |

|                       |               |
|-----------------------|---------------|
| ECLASS-13.0           | 27371232      |
| ECLASS-14.0           | 27371232      |
| ETIM-5.0              | EC001152      |
| ETIM-6.0              | EC001152      |
| ETIM-7.0              | EC001152      |
| ETIM-8.0              | EC001152      |
| customs tariff number | 85319000      |
| EAN                   | 4048879758895 |
| Packaging unit        | 1             |

**Electrical data | Supply**

|                           |        |
|---------------------------|--------|
| Operating voltage DC      | 24 V   |
| Operating voltage DC min. | 21,6 V |
| Operating voltage DC max. | 26,4 V |

**Device protection | Electrical**

|                                        |                  |
|----------------------------------------|------------------|
| Degree of protection (EN IEC 60529)    | IP65             |
| Additional condition protection degree | locked, inserted |

**Mechanical data | Material data**

|                  |         |
|------------------|---------|
| Material housing | Plastic |
| Color housing    | black   |

**Mechanical data | Mounting data**

|        |        |
|--------|--------|
| Height | 122 mm |
| Width  | 88 mm  |
| Depth  | 70 mm  |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -30 °C |
| Operating temperature max. | 60 °C  |

**Connection type 1**

|                          |               |
|--------------------------|---------------|
| Family construction form | M12           |
| No. of poles             | 8             |
| Coding                   | A             |
| Gender                   | male          |
| PIN 1                    | 24 V DC / 0 V |
| PIN 2                    | LED-Modul RD  |
| PIN 3                    | 0 V / 24 V DC |
| PIN 4                    | LED-Modul CL  |
| PIN 5                    | LED-Modul YE  |
| PIN 6                    | LED-Modul BU  |
| PIN 7                    | LED-Modul GN  |
| PIN 8                    | Buzzer        |