

MODLINK MSDD FRAME DBL GREY

with customized printing

Art.No.: 400C-68524-0000001  
Weight: 0.169 kg  
Country of origin: US  
Model designation: Rahmenmodul 2-fach grau customized


Customized printing  
Frame: plastic PA black  
Lid: plastic, PBT gray  
Closure: 3 mm double bit  
with attachable rotation knob

Link to Product

Illustration



Product may differ from Image



Header

Material short text                      Rahmenmodul 2-fach grau customized

Commercial data

|               |                                                    |
|---------------|----------------------------------------------------|
| URL Webshop   | https://shop.murrelektronik.com/400C-68524-0000001 |
| GTIN          | 4048879652667                                      |
| ECLASS-6.0    | 27189217                                           |
| ECLASS-6.1    | 27189260                                           |
| ECLASS-7.0    | 27189260                                           |
| ECLASS-7.1    | 27189260                                           |
| ECLASS-8.0    | 27189260                                           |
| ECLASS-8.1    | 27189260                                           |
| ECLASS-9.0    | 27182810                                           |
| ECLASS-9.1    | 27189260                                           |
| ECLASS-10.0.1 | 27182810                                           |
| ECLASS-10.1   | 27182810                                           |
| ECLASS-11.0   | 27182810                                           |
| ECLASS-11.1   | 27182810                                           |
| ECLASS-12.0   | 27182810                                           |
| ECLASS-13.0   | 27182810                                           |
| ECLASS-14.0   | 27182810                                           |
| ETIM-5.0      | EC002625                                           |
| ETIM-6.0      | EC002625                                           |

|                       |               |
|-----------------------|---------------|
| ETIM-7.0              | EC002625      |
| ETIM-8.0              | EC002625      |
| customs tariff number | 85389099      |
| EAN                   | 4048879652667 |
| Packaging unit        | 1             |

**Device protection | Electrical**

|                                     |      |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP65 |
|-------------------------------------|------|

**Mechanical data | Material data**

|                  |       |
|------------------|-------|
| Material housing | PA    |
| Color housing    | black |
| Material lid     | PBT   |
| Color cover      | gray  |

**Mechanical data | Mounting data**

|                                               |        |
|-----------------------------------------------|--------|
| Height                                        | 127 mm |
| Width                                         | 131 mm |
| Depth                                         | 43 mm  |
| Suitable for installation wall thickness min. | 1 mm   |
| Suitable for installation wall thickness max. | 5 mm   |

**Environmental characteristics | Climatic**

|                                          |        |
|------------------------------------------|--------|
| Operating temperature min.               | -30 °C |
| Operating temperature max.               | 70 °C  |
| Ambient temperature (storage, transport) | -30 °C |

**Frame**

|                                               |        |
|-----------------------------------------------|--------|
| Material housing                              | PA     |
| Color housing                                 | black  |
| Material lid                                  | PBT    |
| Color cover                                   | gray   |
| Suitable for installation wall thickness min. | 1 mm   |
| Suitable for installation wall thickness max. | 5 mm   |
| Degree of protection (EN IEC 60529)           | IP65   |
| Operating temperature min.                    | -30 °C |
| Operating temperature max.                    | 70 °C  |
| Storage temperature min.                      | -30 °C |