

MIIW ANALOG COUPLER COMPONENT

IN: 0(4)..20 mA - OUT: 0(4)..20 mA

Art.No.: 44226

Weight: 0.034 kg

Country of origin: CZ

Model designation: MIIW 0/4-20MA --- 0/4-20MA

INPUT: 0...20 mA



OUTPUT: 0...20 mA

Screw terminals

Input and output galvanically separated

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text

MIIW 0/4-20MA --- 0/4-20MA

Commercial data

URL Webshop	https://shop.murrelektronik.com/44226
GTIN	4048879028431
ECLASS-6.0	27210990
ECLASS-6.1	27210902
ECLASS-7.0	27210902
ECLASS-7.1	27210902
ECLASS-8.0	27210902
ECLASS-8.1	27210902
ECLASS-9.0	27210902
ECLASS-9.1	27210902
ECLASS-10.0.1	27210902
ECLASS-10.1	27210902
ECLASS-11.0	27210902
ECLASS-11.1	27210902
ECLASS-12.0	27210902
ECLASS-13.0	27210902
ECLASS-14.0	27210902
ETIM-5.0	EC002477
ETIM-6.0	EC002477
ETIM-7.0	EC002477
ETIM-8.0	EC002477
customs tariff number	85437090
EAN	4048879028431
Packaging unit	1

Electrical data

Accuracy (of full scale)	0,5 %
--------------------------	-------

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	19,2 V
Operating voltage DC max.	28,8 V
Operating current min.	50 mA
Operating current max.	70 mA

Electrical data | Input

Working resistance max.	250 Ω
-------------------------	-------

Electrical data | Output

Output current max.	0,025 A
Working resistance max.	500 Ω

Industrial Communication

Transmission frequency max.	500 Hz
-----------------------------	--------

Device protection | Electrical

Rated surge voltage	1,5 kV
---------------------	--------

Mechanical data | Mounting data

Height	91 mm
Width	6,2 mm
Depth	71 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	50 °C
Ambient temperature (storage, transport)	-40 °C

Connection type 5

Family construction form	terminal
No. of poles	1
Gender	female
Connection	Screw terminals SK
PIN 1	GD 1
Family construction form	terminal
No. of poles	1
Gender	female
Connection	Screw terminals SK
PIN 1	In
Family construction form	terminal
No. of poles	1
Gender	female
Connection	Screw terminals SK
PIN 1	+ 24 V DC
Family construction form	terminal
No. of poles	1
Gender	female
Connection	Screw terminals SK
PIN 1	OUT
Family construction form	terminal
No. of poles	1
Gender	female
Connection	Screw terminals SK
PIN 1	GD