

product type designation

product description



IE FC TP Robust Standard Cable GP 2x2 (Type A)

Standard bus cable (4-core), sold by the meter, unassembled

Industrial Ethernet FastConnect TP robust Standard GP cable 2x2 (PROFINET Type A), TPE protective jacket, fixed installation for connection to FC RJ45 Plug and FC Outlet RJ45, for universal use, 4-core, shielded Cat5e, sold by the meter, delivery unit max. 2000 m minimum order quantity 20 m .

product brand name

SIMATIC NET

Technical Product Detail Page

<https://i.siemens.com/1P6XV1841-2A>

suitability for use

Standard cable with rigid cores for fast installation

cable designation

SF/UTP, 2YH (ST) C99Y 2x2x0,64/1,5-100 GN

wire length

sold by the meter

electrical data

attenuation factor per length

- at 10 MHz / maximum
- at 100 MHz / maximum

0.065 dB/m
0.22 dB/m

impedance

- at 1 MHz ... 100 MHz

100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz

15 %

near-end crosstalk per length

- at 1 MHz ... 100 MHz

0.5 dB/m

transfer impedance per length / at 10 MHz

10 mΩ/m

loop resistance per length / maximum

115 mΩ/m

operating voltage

- RMS value

80 V

NVP value in percent

69 %

mechanical data

number of electrical cores

4

design of the shield

SF/UTP, overlapped aluminum-clad foil, sheathed in a protective braided shield of tinned copper wires

type of electrical connection / FastConnect

Yes

core diameter

- of AWG22 insulated conductor

0.64 mm

outer diameter

- of inner conductor
- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

0.64 mm
1.5 mm
3.9 mm
6.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

polyethylene (PE)
FRNC
TPE (FR-TPE)

color	
• of the insulation of data wires • of cable sheath	white/yellow/blue/orange green
bending radius	
• with single bend / minimum permissible • with multiple bends / minimum permissible	26 mm 52 mm
tensile load / maximum	150 N
weight per length	59 kg/km
ambient conditions	
ambient temperature	
• during operation • during storage • during transport • during installation • note	-40 ... +75 °C -40 ... +75 °C -40 ... +75 °C -20 ... +60 °C electrical properties measured at 20 °C
fire behavior	flame resistant according to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil • to grease • to water	oil resistant according to DIN EN 50290-2-22 (VDE 0819), (7x24h/90°C), UL13 Sec.40 (96h/100°C) Conditional resistance conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
• halogen-free • PoE capability • PoE+ capability • silicon-free	No Yes Yes Yes
wire length / for Industrial Ethernet	
• with 100BaseTX	100 m
test voltage	
• at AC / core-to-core • at AC / core shield	2000 V 2000 V
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CM, PLTC, SUN RES
UL/ETL style / 600 V Rating	No
certificate of suitability	
• EAC approval • CE marking • RoHS conformity	Yes Yes Yes
standard for structured cabling	Cat5e
• resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS)	No No No No No No No
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to web page: SiePortal • to website: Image database	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb

- to website: CAX-Download-Manager
- to website: Industry Online Support

<https://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Declaration of Conformity](#)

[China RoHS](#)

General Product Approval

other

Environment

Industrial Communication

[Fire safety / Physical security](#)

[Miscellaneous](#)

[Environmental Conformations](#)

[Environmental Conformations](#)

[PROFINET](#)

last modified:

3/10/2026