

**MVP12, 6XM12, MOSA, PLUGGABLE CABLE**

5.0m PUR-JB 12x0,34+5x0,75

Art.No.: 4927076

Weight: 1.285 kg

Country of origin: DE

Model designation: MVM6-VHB5.0

6-way, 5-pole, MOSA

PUR/PVC (UL/CSA)

5.0 m



potentially separated

with LED for digital PNP-signals 24 V DC

quick connection elements included

[Link to Product](#)

**Illustration**



Product may differ from Image

**Header**

Material short text MVM6-VHB5.0

**Commercial data**

URL Webshop <https://shop.murrelektronik.com/4927076>

GTIN 4048879057608

ECLASS-6.0 27279219

ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440108
ECLASS-9.1	27440108
ECLASS-10.0.1	27440108
ECLASS-10.1	27440108
ECLASS-11.0	27440108
ECLASS-11.1	27440108
ECLASS-12.0	27440108
ECLASS-13.0	27440108
ECLASS-14.0	27440108
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879057608
Packaging unit	1

**Electrical data | Supply**

Operating voltage DC	24 V
Current operating per contact max.	4 A
Total current at 1 time current feed-in max.	8 A
Total current at 2 times current feed-in max.	16 A

**Industrial Communication**

Number of signals per port	2
----------------------------	---

**Installation**

Connection cross section min.	0,25 mm <sup>2</sup>
Connection cross section max.	0,5 mm <sup>2</sup>

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	mounted, screwed

**Device protection | Media**

Flame resistance	flame retardant
------------------	-----------------

**Mechanical data | Material data**

Material housing	Plastic
------------------	---------

**Mechanical data | Mounting data**

Height	43 mm
Width	50,2 mm
Depth	122 mm
Mounting method	Cap nut

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	80 °C