

RMMDUE 11/230 V AC INPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/DC / 5 A

Art.No.: 51138

Weight: 0.002 kg

Country of origin: CZ



Model designation: RMMDUE 11/230 V AC

1 relay; 1 NO/NC contact

5 A

230 V AC

with minus plug link

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RMMDUE 11/230 V AC

Commercial data

URL Webshop	https://shop.murrelektronik.com/51138
GTIN	4048879027748
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027748
Packaging unit	1

Electrical data | Input

Input voltage AC	230 V
Input voltage AC min.	195 V
Input voltage AC max.	253 V
Input voltage DC	230 V
Input voltage DC min.	195 V
Input voltage DC max.	253 V
Input current	4,5 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	5 A
Switching current DC	1 mA
Switching frequency max.	15 Hz
Power rating AC max.	1.500 VA
Power rating DC max.	180 W
Switching capacity AC-12 (EN IEC 60947-5-1)	5 A (24/110/230 V AC)
Utilization category AC-15 (EN IEC 60947-5-1)	4 A @ 24 V 4 A @ 110 V 4 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V 0.25 A @ 110 V 0.1 A @ 230 V

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data	
Response time max.	10 ms
Drop-out time max.	10 ms
Bounce time max.	1 ms
Mechanical data Material data	
Material contact	Ag hv, Ag Ni 0.15 hv
Mechanical data Mounting data	
Height	82 mm
Width	12 mm
Depth	68 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715), G32
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 3	
Connection type 1	X1
Connection type 2	X2
Connection type 3	X3
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 2
PIN 2	A 1
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	12
PIN 2	14
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	11
PIN 2	11