

product type designation	IE TP Cord PLUS RJ45/RJ45
product description	Patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)
	IE TP Cord PLUS RJ45/RJ45, Cat6a, S/FTP cable 4x2, pre-assembled with 2 RJ45 plugs for EasyClip interlock length 2 m.
product brand name	SIMATIC NET
Technical Product Detail Page	https://i.siemens.com/1P6XV1870-4HH20
suitability for use	easy connection of end devices to the IE FC cabling system with EasyClip interlock
cable designation	S/FTP, LI 02YSCH 4x2x0,15 PIMF GN FRNC
wire length	2 m
electrical data	
number of electrical connections	2
attenuation factor per length	
• at 10 MHz / maximum	0.086 dB/m
• at 100 MHz / maximum	0.28 dB/m
• at 300 MHz / maximum	0.485 dB/m
• at 600 MHz / maximum	0.675 dB/m
impedance	
• at 1 MHz ... 100 MHz	100 Ω
• at 10 MHz ... 600 MHz	100 Ω
relative symmetrical tolerance	
• of the characteristic impedance at 1 MHz ... 100 MHz	5 %
coupling loss / at 30 MHz ... 100 MHz / minimum	85 dB
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	290 mΩ/m
operating voltage	
• RMS value	80 V
NVP value in percent	76 %
mechanical data	
number of electrical cores	8
design of the shield	S/FTP, overlapped aluminum-clad foil, sheathed in a protective braided shield of tinned copper wires
core diameter	
• of AWG26 insulated conductor	0.5 mm
outer diameter	
• of inner conductor	0.5 mm
• of the wire insulation	1 mm
• of cable sheath	6.2 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.3 mm
material	
• of the wire insulation	polyethylene (PE)
• of cable sheath	FRNC
color	
• of the insulation of data wires	white/blue, white/orange, white/green, white/brown
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	31 mm
• with multiple bends / minimum permissible	62 mm
weight per length	46 kg/km
plug	
connector type	RJ45

type of plug interlock	latched
design of plug-in connection	RJ45-180
ambient conditions	
ambient temperature - during operation - during storage - during transport - during installation - note	-25 ... +80 °C -25 ... +80 °C -25 ... +80 °C -25 ... +80 °C In fixed installation -40 °C to 80 °C
fire behavior	flame resistant acc. to IEC 60332-1-2, EN 60332-3-24, smoke density acc. to IEC 61034
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance - to mineral oil - to grease	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature - halogen-free - PoE capability - PoE+ capability - PoE++ capability - silicon-free	Yes; halogen-free according to EN 60754-2 Yes Yes Yes Yes
test voltage - at AC / core-to-core - at AC / core shield	500 V 1500 V
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	Yes; E502506 AWM STYLE 21279, Wiring Harness
certificate of suitability - EAC approval - UL approval - RoHS conformity	ISO/IEC 11801-1, IEC 61035 Yes Yes Yes
standard for structured cabling	Cat6A
Marine classification association - American Bureau of Shipping Europe Ltd. (ABS) - French marine classification society (BV) - Det Norske Veritas (DNV) - Germanische Lloyd (GL) - Lloyds Register of Shipping (LRS) - Nippon Kaiji Kyokai (NK) - Polski Rejestr Statkow (PRS)	No No No No No No No
further information / internet links	
internet link - to website: Selection guide for cables and connectors - to web page: selection aid TIA Selection Tool - to web page: SiePortal - to website: Image database - to website: CAX-Download-Manager - to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or

network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



last modified:

6/29/2026 