

RMM 11/230 V OUTPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/DC / 6 A

Art.No.: 51515

Weight: 0.030 kg

Country of origin: CZ



Model designation: RMM 11/230 V

1 relay; 1 NO contact

6 A

230 V AC

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RMM 11/230 V

Commercial data

URL Webshop	https://shop.murrelektronik.com/51515
GTIN	4048879027557
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027557
Packaging unit	1

Electrical data | Input

Input voltage AC	230 V
Input voltage AC min.	195 V
Input voltage AC max.	250 V
Input voltage DC	230 V
Input voltage DC min.	195 V
Input voltage DC max.	250 V
Input current	3,5 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	6 A
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1.250 VA
Power rating DC max.	240 W
Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24 V 6 A @ 110 V 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	4 A @ 24 V 4 A @ 110 V 4 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V 0.25 A @ 110 V 0.1 A @ 230 V

Diagnostics

Status indication LED	red
-----------------------	-----

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data

Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1,5 ms

Mechanical data | Material data

Material contact	Ag hv, Ag Ni 0.15 hv
------------------	----------------------

Mechanical data | Mounting data

Height	56 mm
Width	12 mm
Depth	65 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715), G32

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Connection type 2

Connection type 1	X1
Connection type 2	X2
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 2
PIN 2	A 1
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	13
PIN 2	14